



KC22B1



Active

KC22B1

Mechanical Grounding Connector, Cable to Flat, 10 - 3 AWG (Str) / 10 - 2 AWG (Sol), 3/8" Stud

[Image](#) | [Line Art](#) | [3D Model](#) | [Video](#) | [Customer Drawing](#)

 [Email Datasheet](#)

 [Print Datasheet](#)

Specifications

Documents

Dimensional	General	Conductor(s)	Physical	Approvals / Certifications	Other Features
Dimensional					
Stud Length (in)	31/32,0.96				
Thread Size	3/8-16				
Length (in)	2.12				
Height (in)	1.00				
D or Diameter (Fraction) (in)	1-1/8				
Nut Width (Fraction)	3/4				
Nut Width (in)	0.75				
D - in	1.13				
Body Width (Fraction)	5/8				
Body Width (in)	0.62				
Height (Fraction) (in)	1				
General					
Product Description	Mechanical Grounding Connector, Cable to Flat, 10 - 3 AWG (Str) / 10 - 2 AWG (Sol), 3/8" Stud				
Conductor(s)					
Copper Solid Size (Range)	10 AWG-2 AWG				
Copper Stranded (Range)	10 AWG-3 AWG				
Physical					
Type of Plating	Unplated				
Plated (Yes or No)	N				
Product Material	Leaded Bronze Alloy				
Approvals / Certifications					
Rated for Direct Burial	Y				
UL Listed	Y				
CSA Certified	Y				
ROHS Compatible	Exempt				
UL Recognized	N				
CULUS	N				
Industry Standards	UL467				
Other Features					
UPC	7818102550566				

