



YA31LNT38, 350 kcmil, CU, 1 Hole, 3/8 Stud, Std, Narrow

By Burndy
Catalog # [YA31LNT38](#)

350 kcmil, CU, 1 Hole, 3/8 Stud, Standard Barrel, Inspection Window, Narrow Tongue

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	UL 486A-486B
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	350 KCMIL
Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	350 (91) Navy
Conductor - Copper Str Navy Size Range	350 (91) Navy
Conductor Size	350 KCMIL
Conductor - Copper Str Size Range	350 kcmil
Conductor Type	CODE

Configuration

Physical Attribute - Number of Holes	1
Connector Type	STANDARD BARREL

Current

Voltage - Maximum	35000
Voltage Rating	35 kV

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.88 in
Dimension - L Length Overall mm	84 mm
Dimension - Pad Width inch	0.96 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - Strip Length inch	1-3/16 in
Dimension - Stud Size fraction	3/8
Dimension - Stud Size inch	3/8
Dimension - B Length fraction	1-1/16 in
Dimension - B Length inch	1.06 in
Dimension - Z inch	1.04 in
Physical Attribute - Tongue Angle	Straight
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Length Overall inch	3.31 in
Dimension - D inch	1.45 in
Dimension - N inch	0.41 in

General

Die Index	18
Trade Name	HYLUG™
Sub Brand	HYLUG
Color Code	Red
Physical Attribute - Tongue Type	Standard
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Type	YA-L-NT, Code Conductor Standard Barrel Narrow Tongue

UPC 14 Digit GTIN
Material
Plating Type
Finish Type
UPC

00781810018569
COPPER
Tin - Electro Plated
Tin-Plated
781810018569

Carton Quantity 100
Pallet Quantity 9600

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)
[Installation Manual \[French, English\]](#)

Logistics

Minimum Pack Quantity 1

 **A Hubbell brand**

© 2026 Hubbell Incorporated. All rights reserved
BRDY-YA31LNT38-SPEC-EN | REV 4/2026