Part Number: 170807-2017

Neoscale Plug Assy 100ohm 18mm 6X20



Series image - Reference only

Status: Active
Series: 170807
Category: Molex Parts

Go to **Part Detail**▼

CHECK DISTRIBUTOR INVENTORY

Add to My Parts

Sales Drawings, 3D Models, and Brochures

Drawing (PDF)

Note - Please disable browser pop-up blockers to view documents on www.molex.com

Application Tooling

FAQ

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling
Check our list of old tooling that used to be available for this part

Product Environmental Compliance

EU ELV: Not Relevant

EU RoHS: Compliant

EU RoHS Phthalates: Not Contained

China RoHS:

REACH SVHC: Not Contained Per - ED/30/2017 (7 July 2017)

Low-Halogen Status: Low-Halogen

Product Compliance Statement

EU RoHS Certificate of Compliance (PDF)

Multiple Part Product Compliance Statements
EU RoHS, REACH SVHC, & Low-Halogen

Multiple Part Industry Compliance Documents

*IPC 1752A Class C
*IPC 1752A Class D
*Molex Product Compliance Declaration

Questions on Product Environmental Compliance? Email ProductCompliance@molex.com

Request Molex's CMRT from conflictminerals@molex.com

Part Detail

COLLAPSE ALL

General

Status	**Active**
Category	Molex Parts
Series	170807
UPC	889056154765

Physical

Net Weight	28.829/g

Solder Process Data

Solderability Shelf Life Statement	
Duration at Max. Process Temperature (seconds)	020
Lead-freeProcess Capability	REFLOW
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260

Downloaded from Arrow.com.

Molex is a registered trademark of Molex, LLC in the United States of America and may be registered in other countries; all other trademarks listed herein belong to their respective owners.

© Copyright 2017

Downloaded from Arrow.com.