

[Request more info](#)

Part Number : 5690117000F



C17339



This is a
RoHS Compliant Product
[To learn more click here](#)

General Description

Series	569
Configuration	3 mm Lens
Description	3 mm Bi-Level CBI O-X
Package Options	Bulk Packaging
Sizes	3mm
Lamp Type	Bi-Level Housing
Viewing	Right Angle
Polarity	Cathode Pin 1 & 3
Lens Style	Tinted, Diffused
Viewing Angle	60
LED Centerline	2.29mm

Absolute Maximum Ratings (Ta = 25°)

Solder Temperature	260 for 5 secs
Operating Temperature	-55 to +100
Storage Temperature	-55 to +100

Operating Characteristics

Peak Wave Length	600	
LED Position	1	2
Luminous Intensity Min	3.4	
Luminous Intensity Typical	7	
Forward Voltage Typical	1.9	
Forward Voltage Max	2.4	
Test Current mA	10mA	
Power Dissipation Max	135mW	