



Representative



Line Art

Catalog Number: 54804
Product ID: 7TAH007510R0000
UPC Number: 78621054804
EAN Number: 05414363110712
Status: A

Copper Two-Way Splice, Long Barrel, Max 35kV, Wire Size #8 AWG, Length 1.75 Inches, Diameter 0.27 Inch, Tin Plated, Die Code 21, Die Color Code Red

- Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.

North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Sub Brand	Color Keyed
Type	Splice Connector
Special Features	Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.
Standard	UL E9809
Conductor Range	8-8
Material	Copper
Finish	Tin-Plated
Color	Red
Voltage Rating	600 V
Insulation	None

European Specifications (ETIM)

ETIM	EC001059 Crimp splices for copper conductor
Sleeve form	Long
Material	Copper
Surface protection	Tinned
Insulation	None
Voltage row	Up to 35kV
Type of connection	End connector

Packaging

Inner Quantity	50
Inner Dimensions (inches)	3.3x2.8x2.3
Outer Quantity	500
Outer Dimensions (inches)	12.5x6.4x4
Weight Uom	2 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000666
Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website
Instruction Sheet	TA00674-TB2

For further technical assistance, please contact us...

ABB Installation Products - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com