





APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/3/16	
A		REVISED DIM.	6/16/16	HR



SPECIFICATIONS:

Material:
 Insulator: Hi-temp thermoplastic, rated UL 94V-0
 Insulator color: Black
 Contacts: Brass
 Plating:
 Gold flash over Nickel underplate overall
 Electrical:
 Current rating: 1.0 Amp
 Contact resistance: 20 mohms max
 Insulation resistance: 1,000 Mohms
 Dielectric withstanding voltage: 500 VAC/DC
 Temperature Rating:
 Operating temperature: -40°C to +105°C
 Environmental:
 Lead free, RoHS compliant



Positions: 10, 14, 16, 20, 24, 26, 30, 32, 34, 40, 44, 50, 60, 64, 80, 100
 A = .050 [1.27] x No. of Spaces
 B = .050 [1.27] x No. of Positions per Row + .177 [4.50]
 C = .050 [1.27] x No. of Positions per Row + .244 [6.20]

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
.X	± .10	Ø.X	± .10				
.XX	± .020	Ø.XX	± .015				
.XXX	± .015	Ø.XXX	± .010				
APPROVALS				TITLE			
DRAWN				.050" x .050" BOX HEADER, VERTICAL MOUNT			
CHECKED				GOLD PLATED			
APPROVED				SIZE			
				X			
				PART NO.			
				HBHR-B1-XX-VG			
				REV.			
				A			
				REF: S00019C			
				SCALE: NTS			
				SHEET 1 OF 1			