

[Precautions for use](#)
[General notes](#)

F-400-01A1 made in JAPAN



Bayonet Cap

Electric shock safety

2020-01-09

[Notice of partial product changes.](#) PDF

[See other change notifications](#)


E101405



40012892



Order model number

Order model number F-400-01A1

Order example F-400-01A1

[Basic information](#)
[Dimension](#)
[Soldering heat resistance conditions](#)
[Conformity product / Mate product](#)
[Download](#)

Mating fuse size

6.4mm × 30mm

6.35mm × 30mm

6.35mm × 31.8mm

Basic information

Rating	250V-10A
Insulation resistance	DC500V, 100MΩ Min
Withstand voltage	AC2000V (1minute)
Certificates & Approvals	UL-CSA(C-UL)-VDE
Main insulator	Phenolic (UL94V-0)
Cap insulator	PBT (UL94V-0)
Terminal type	Both soldering and 0.187in. tab terminal (t0.5mm(0.020in.)) for quick-connect terminations.
Body color	B (Black)
Cap color	W (White)
Panel thickness	7.5mm Max
Nut torque	0.8N·m
Applicable tool for cap	Screw driver

List of partial product change notifications

2020-01-09	Notice of partial product changes. PDF
2019-08-01	Notice of partial product changes. PDF
2017-09-06	Notice of partial product changes. PDF
2009-12-15	Notice of partial product changes. PDF
2009-12-15	Notice of partial product changes. PDF

Related products

F-130


[F-130](#)
[Add to My List](#)
[Home](#)
[Product search](#)
[Product Category](#)
[About SATO PARTS](#)
[Contact us](#)
[Download brochure](#)
[Environmental initiatives](#)
[Privacy policy](#)
[Download terms](#)
[Terms of Use](#)
[Site map](#)