



DATE	REV	ECN	APP'D. BY
08/31/17	A0	Released	JRC
09/18/17	A1	11095	GWL
04/03/18	A2	11218	GWL
12/04/19	A3	11483	ADB



Notes:

- Each cable assembly to be individually bagged.
- Cable Construction USB 2.0 UL Style 1
 - 28 AWG 1 Twisted Pair
 - 26 AWG x 2C
 - AMA BRAID
 - 4.5mm OD
 - Black PVC Jacket
- CONNECTOR P1:USB A Male 2.0 White Insulator, Gold flash on contacts, Nickel Plated Shell
- CONNECTOR P2:USB B Male 2.0 White Insulator, Gold flash on contacts, Nickel Plated Shell
- Hood P1 & P2: Molded Beige PVC Strain Relief
- All cables tested for Continuity & Shorts

P/N Key:

SC-2AMKxxxF


Length

- 001 = 1 Ft
- 003 = 3 Ft
- 006 = 6 Ft

O/A Length Tolerance:

Metric	
0 ~ 200mm	±10mm
201 ~ 1000mm	±20mm
1001 ~ 1500mm	±25mm
1501 ~ 2100mm	±30mm
>2100mm	±40mm
Imperial	
0 ~ 1ft	±0.5in
2ft ~ 3ft	±0.75in
4ft ~ 7ft	±1.0in
> 7ft	±1.5in

Wiring Map: USB 2.0 Hi-Speed



Example Parts Numbers

Feet	
P/N	Length
SC-2AMK001F	1'
SC-2AMK003F	3'
SC-2AMK006F	6'

For Part Numbers Not Shown Follow Part Number Key Format



THIRD ANGLE PROJECTION

DO NOT SCALE DRAWING

DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE

DIMENSIONS: INCHES [METRIC]

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ±.005 [0.13] ANGLES ARE ± 1°

SHEET NO. 1 OF 1



11118 Susquehanna Trail South
Glen Rock, PA 17327-9199
(717) 235-7512
<http://www.stewartconnector.com>

TITLE:
Cable Assembly, USB 2.0, Type A/M-Type Micro B/M, Black

THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF STEWART CONNECTOR AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN CONSENT OF STEWART CONNECTOR

DRN BY: KAC

DATE 08/30/17

APPD BY: JRC

DATE 08/31/17

DWG NO. CT999154

REV. A3