
PANDUCT® Type E — Slotted Wall Wiring Duct



Type E Slotted Wall Wiring Duct


- Made of rigid PVC (See *pg. 34* for material specifications)
- Rated for continuous use temperatures up to 50°C (122°F)
- Available in a variety of colors as a standard part (See *page 36* for details)
- Provided with standard mounting holes (dimensions *page 31*)
- Available without mounting holes (See ordering information below)
- Available with adhesive backing* (See *page 22* for details)

Type E— Wiring Duct Standard Colors†:

LG	DG	WH
Light Gray	Dark Gray	White

BL	IB
Black	IntrinsicBlue

Colors shown are approximate.



Duct Part Number	Duct External Dimensions		Cover Part Number	Duct Std. Ctn. Qty.	Cover Std. Ctn. Qty.	Std. Lgth
	WxH IN.	WxH (mm)				
E.5X.5LG6	0.63 x 0.56	(16.0) x (14.2)	C.5LG6	120 ft.	120 ft.	6 ft.
E.5X.62LG6	0.63 x 0.68	(16.0) x (17.3)		120 ft.	120 ft.	
E.5X1LG6	0.63 x 1.06	(16.0) x (26.9)		120 ft.	120 ft.	
E.5X1.25LG6	0.63 x 1.31	(16.0) x (33.3)		120 ft.	120 ft.	
E.5X1.75LG6	0.63 x 1.81	(16.0) x (46.0)		120 ft.	120 ft.	
E.5X2LG6	0.63 x 2.06	(16.0) x (52.3)		120 ft.	120 ft.	
E.75X.75LG6	0.88 x 0.81	(22.4) x (20.6)	C.75LG6	120 ft.	120 ft.	6 ft.
E.75X1LG6	0.88 x 1.06	(22.4) x (26.9)		120 ft.	120 ft.	
E.75X1.5LG6	0.88 x 1.56	(22.4) x (39.6)		120 ft.	120 ft.	
E.75X2LG6	0.88 x 2.12	(22.4) x (53.8)		120 ft.	120 ft.	
E1X1LG6	1.14 x 1.12	(29.0) x (28.4)	C1LG6	120 ft.	120 ft.	6 ft.
E1X1.25LG6	1.14 x 1.37	(29.0) x (34.8)		120 ft.	120 ft.	
E1X1.5LG6	1.14 x 1.62	(29.0) x (41.1)		120 ft.	120 ft.	
E1X2LG6	1.14 x 2.12	(29.0) x (53.8)		120 ft.	120 ft.	
E1X2.5LG6	1.14 x 2.62	(29.0) x (66.5)		120 ft.	120 ft.	
E1X3LG6	1.14 x 3.12	(29.0) x (79.2)		120 ft.	120 ft.	
E1X4LG6	1.14 x 4.12	(29.0) x (104.6)		120 ft.	120 ft.	
E1.5X1 LG6	1.64 x 1.12	(41.7) x (28.4)	C1.5LG6	120 ft.	120 ft.	6 ft.
E1.5X1.5LG6	1.64 x 1.62	(41.7) x (41.1)		120 ft.	120 ft.	
E1.5X2LG6	1.64 x 2.12	(41.7) x (53.8)		120 ft.	120 ft.	
E1.5X3LG6	1.64 x 3.12	(41.7) x (79.2)		120 ft.	120 ft.	
E1.5X4LG6	1.64 x 4.12	(41.7) x (104.6)		60 ft.	120 ft.	
E2X1LG6	2.14 x 1.12	(54.4) x (28.4)	C2LG6	120 ft.	120 ft.	6 ft.
E2X1.5LG6	2.14 x 1.62	(54.4) x (41.1)		120 ft.	120 ft.	
E2X2LG6	2.14 x 2.12	(54.4) x (53.8)		120 ft.	120 ft.	
E2X2.5LG6	2.14 x 2.62	(54.4) x (66.5)		60 ft.	120 ft.	
E2X3LG6	2.14 x 3.12	(54.4) x (79.2)		60 ft.	120 ft.	
E2X4LG6	2.14 x 4.12	(54.4) x (104.6)		60 ft.	120 ft.	
E2X5LG6	2.14 x 5.12	(54.4) x (130.0)		60 ft.	120 ft.	
E2.5X3LG6	2.64 x 3.12	(67.1) x (79.2)	C2.5LG6	60 ft.	120 ft.	6 ft.
E3X1LG6	3.14 x 1.12	(79.8) x (28.4)	C3LG6	120 ft.	120 ft.	6 ft.
E3X1.25LG6	3.14 x 1.37	(79.8) x (34.8)		120 ft.	120 ft.	
E3X2LG6	3.14 x 2.12	(79.8) x (53.8)		60 ft.	120 ft.	
E3X3LG6	3.14 x 3.12	(79.8) x (79.2)		60 ft.	120 ft.	
E3X4LG6	3.14 x 4.12	(79.8) x (104.6)		60 ft.	120 ft.	
E3X5LG6	3.14 x 5.12	(79.8) x (130.0)		60 ft.	120 ft.	
E4X1.5LG6	4.14 x 1.62	(105.2) x (41.1)	C4LG6	120 ft.	120 ft.	6 ft.
E4X2LG6	4.14 x 2.12	(105.2) x (53.8)		60 ft.	120 ft.	
E4X3LG6	4.14 x 3.12	(105.2) x (79.2)		60 ft.	120 ft.	
E4X4LG6	4.14 x 4.12	(105.2) x (104.6)		60 ft.	120 ft.	
E4X5LG6	4.14 x 5.12	(105.2) x (130.0)		60 ft.	120 ft.	

See *page 31* for complete listing of dimensions. *Adhesive tape is not CSA Certified.

Ordering Information:

- Order number of feet required in multiples of 6 ft or Std. Carton quantities.
- To order duct without mounting holes, add NM to Part Number.
- To order with pressure-sensitive adhesive mounting tape applied, add -A to Part Number.
- Part Number shown for Light Gray LG. To order other colors, substitute WH White, DG Dark Gray, BL Black, and IB Intrinsic Blue

†See *page 36* to determine which sizes are available in each color

Part Number Nomenclature —

E	.5	X	.5	LG	6
type/style	nominal width (in)		nominal height (in)	color	length (ft)

Downloaded from Arrow.com.