



CH7M

by Burndy
Catalog ID: CH7M

Nylon Cable Hanger

Product Details

General

Color	Natural
Material	Nylon 6/6
Mounting Method	Screw
UPC	781810336298

Dimensions

Dimension - Bundle Diameter Max inch	0.44
Dimension - Width inch	0.38 in
Dimension - Width mm	10 mm

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1000
Packaging Type	Bag

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)