





DIMENSIONS mm (inches)



METHOD OF INSERTION
ON THE PCB = FLAT ROCK



PCB LAYOUT



SPECIFICATION 972 or FILF= Nothing in cavities 10 to 17 row a / b / c

LEAD FREE P/N
86093728194755FILF

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C-8609-0000C

rev	ecn no	dr	YY/MM/DD
A	LS08-0148	HLE	2008/04/15
B	LS08-0164	HLE	2008/07/16
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302	tolerance std ISO 406 ISO 1101	projection A3	mm
			TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	LE GALLIC	2008/04/15	ANGULAR 0.XX' ± 2°	0.X	± 0.1	size
Eng	LE GALLIC	2008/04/15		0.XX	± 0.1	A3
Chr	LEGARE	2008/04/15		0.XXX	± 0.1	Scale 1.5
Appr	LEGARE	2008/04/15	Product family		ECN	LS08-0164
			DIN 8609		Spec ref	-
FCI			STRAIGHT RECEPTACLE - STYLE C			Rev.
			PRESS FIT			B
			see table			sheet 1 of 1

REV F - 2006-04-17