

3455R 04210010

[Products](#) > [Sensors](#) > [Humidity, Thermal & Flexible Heater Products](#) > [Thermostats/Thermal Switches](#) > [Commercial](#) > [Automatic Reset](#) > [3455R Series](#) > **3455R 04210010**

Overview

3455R Series Phenolic Automatic Reset Thermostats.
The 3455R Series consists of a temperature-sensitive bimetal disc, electrically isolated from the switch, which actuates the switch.
[View More](#)



Technical Specifications

Functional Properties	Close on rise	Reset Type	Automatic
Operating Temperature	0 °C to 150 °C [32 °F to 302 °F]	Amperage	15 A/10 A resistive max.
Voltage	120 Vac/240 Vac	Open Temperature	18.3 °C [65 °F]
Open Tolerance	2.8 °C [5 °F]	Close Temperature	28.3 °C [83 °F]
Close Tolerance	2.8 °C [5 °F]	Environmental Exposure Range	-18 °C to 177 °C [0 °F to 350 °F]

[View More](#)

View documents in:

English ▾

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
 Commercial Thermostats	Datasheet	English	756KB
 Thermostats Line Guide	Product Line Guide	English	444KB
 Thermal Sensors	Product Range Guide	English	2MB

Product Features

- Cost effective
- Rivet sleeve construction
- High profile
- High current

Applications

- HVAC
- Automotive
- Major appliances
- Office copy machines
- Heat and smoke detectors


view all 3455R 04210010 literature


view distributor inventory


sample request


email support


get support


email sales


find a distributor


email this page

NAVIGATION LINKS

[HOME PAGE](#)

[PRODUCTS](#)

[DISTRIBUTOR INVENTORY](#)

[INDUSTRIES](#)

[SUPPORT](#)

[NEWS & EVENTS](#)

[ABOUT US](#)

DISTRIBUTOR LINKS

[ECOM LOGIN](#)

[LEARN CENTER](#)

[REQUEST ACCESS TO ECOM](#)

[SALES/AD PORTAL LOGIN](#)

[SALES/AD PORTAL ACCESS REQUEST](#)

[SAMPLE REQUEST](#)

[SUPPLIER MICROSITE](#)

LANGUAGE

English 

SOCIAL MEDIA



SITE INFORMATION

[PRIVACY STATEMENT](#)

[SITEMAP](#)

[TERMS & CONDITIONS](#)

[COPYRIGHT © 2018 HONEYWELL
INTERNATIONAL INC.](#)