


EC No.
22595
22615


Push Button Switch





plug and socket device
6-pol in accordance to
DIN 72585 / ISO 15170





Technical Data

Construction

Socket material	PA black
Button material	PMMA black
Protection interior	IP6K9K IEC 60529
connector	IP00 IEC 60529
Max. torque	max. 5 Nm
Weight	30g


Mechanical Data

Pre travel	1,5±0,5mm
Total travel	2,5+0,5mm
Operating force	30 to 45N
Current carrying parts	Cu-alloy
Contact material	Ag-alloy
Mechanical life	100 000 cycles
Temperature Range	-40°C to +90°C


Electrical Data

Voltage Range	9VDC to 32VDC
Electrical load	10mA to 5A

Mounting Dimensions



Circuit Diagram



For this drawing we reserve the copyright
in accordance with DIN ISO 16016

	Date	Name
Create	18.10.2013	Azubi
Edited	26.03.2019	Hamar
Check	27.03.2019	Baumg

mm

Scale 1:1

General Tolerances
DIN ISO 2768 cL

Drawing No:
TS-221-SW11 908

NSN.:

Downloaded from Arrow.com.