

Han 8D male insert crimp w. sealing scre



Image is for illustration purposes only. Please refer to product description.

Part number	09 36 008 3006
Specification	Han 8D male insert crimp w. sealing scre
HARTING eCatalogue	https://harting.com/09360083006

Identification

Category	Inserts
Series	Han D®
Specification	With IP67 fixing screw

Version

Termination method	Crimp termination
Gender	Male
Size	3 A
Number of contacts	8
Details	Please order crimp contacts separately. for thermoplastics and metal hoods/housings

Technical characteristics

Conductor cross-section	0.14 ... 2.5 mm ²
Rated current	10 A
Rated voltage	50 V
Rated voltage	50 V AC 120 V DC
Rated impulse voltage	1.5 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 ... +125 °C



Pushing Performance
Since 1945

Technical characteristics

Mating cycles	≥500
---------------	------

Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	RAL 7032 (pebble grey)
Material (seal)	NBR
Material flammability class acc. to UL 94	HB
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984
	EN 175301-801
Approvals	DNV GL

Commercial data

Packaging size	10
Net weight	8 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140282278
eCl@ss	27440205 Contact insert for industrial connectors
ETIM	EC000438
UNSPSC 24.0	39121522