

## Personal Desktop Charging Station with 2-Outlet Surge Protector, 6 ft. (1.83 m) Cord, 1080 Joules, 4 x USB (4.8A total)

MODEL NUMBER: TLP26USBB



### Highlights

- 2 outlet / 6-ft. cord
- 1080 joule rating
- 4.8 amp quad port USB charger

### Package Includes

- TLP26USBB Personal Desktop Charging Station
- Instruction manual with warranty information

### Description

Tripp Lite's TLP26USBB Personal Desktop Charging Station provides exceptional convenience for daily charging tasks. Perfect for home, office, workstations and dorm rooms. With 2 AC outlets for safe power and 4 USB port with 4.8 amps of total power, this charging station can easily handle multiple devices. The built in slot can hold your tablet or phone for hands free viewing while charging. TLP26USBB Personal Desktop Charging Station offers 2 total outlets, 6 foot cord, 4 USB charging ports for a total of 4.8 amps, and diagnostic LED to warn of suppressor damage. AC suppression rated at 1080 joules shields equipment from surges and line noise. . \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

PLUG/OUTLETS: Input: NEMA5-15P/Output: 6 NEMA5-15R/6-ft. (1.83 m) AC line cord

ELECTRICAL: 120V AC, 60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Corded multi-outlet charging station

SUPPRESSION: AC: 150V RMS Clamping/1080 joules/400V UL60905

### Features

- 2 outlets
- 6-ft. (1.83 m) cord
- 4 USB charging ports - 4.8 amp total
- Built in slot to hold phones and tablets
- Surge suppression rating: 1080 joules
- EMI/RFI noise filtering
- 15 amp resettable circuit breaker
- Green protection LED
- Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
- \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

## Specifications

| OVERVIEW                           |                                                                      |
|------------------------------------|----------------------------------------------------------------------|
| UPC Code                           | 037332183385                                                         |
| Product Type                       | Surge Protector                                                      |
| Charging Form Factor               | Strip                                                                |
| Device Compatibility               | Phone; Tablet; Amazon Kindle                                         |
| INPUT                              |                                                                      |
| Nominal Input Voltage(s) Supported | 120V AC                                                              |
| Recommended Electrical Service     | 120V (110-125V)                                                      |
| Input Cord Gauge Type              | 16 gauge; SJT                                                        |
| Input Cord Gauge (AWG)             | 16; SJT                                                              |
| Voltage Compatibility (VAC)        | 120                                                                  |
| Input Plug Type                    | NEMA 5-15P                                                           |
| Input Cord Details                 | SJT                                                                  |
| Input Cord Length (ft.)            | 6                                                                    |
| Right-Angle Plug                   | Yes                                                                  |
| Input Cord Length (m)              | 1.83                                                                 |
| Integrated Cord Clip               | No                                                                   |
| OUTPUT                             |                                                                      |
| Frequency Compatibility            | 60 Hz                                                                |
| Output Receptacles                 | (2) 5-15R                                                            |
| Circuit Breaker (amps)             | 15                                                                   |
| Right-Angle Outlets                | No                                                                   |
| USER INTERFACE, ALERTS & CONTROLS  |                                                                      |
| Diagnostic LED(s)                  | Yes                                                                  |
| Diagnostic LED Details             | Built-in LED confirms suppressor "protection present" (green) status |
| CHARGING                           |                                                                      |
| Number of Charging Ports           | 4                                                                    |
| Total Charging Watts               | 24                                                                   |
| Charging Method                    | USB                                                                  |
| Charging Port Type                 | USB A (FEMALE)                                                       |
| Charging Ports / Amps              | (4) 4.8A                                                             |

|                                      |                                                                              |
|--------------------------------------|------------------------------------------------------------------------------|
| Overcharge Protection                | No                                                                           |
| <b>SURGE / NOISE SUPPRESSION</b>     |                                                                              |
| AC Suppression Joule Rating          | 1080                                                                         |
| AC Suppression Response Time         | < 1 ns                                                                       |
| Protection Modes                     | Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression |
| UL1449 Let Through Rating            | 400V                                                                         |
| EMI / RFI Filtering                  | Yes                                                                          |
| Automatic Shut-Off                   | Yes                                                                          |
| <b>DATALINE SURGE SUPPRESSION</b>    |                                                                              |
| Cable (Coax) Protection              | No                                                                           |
| Network (Ethernet) Protection        | No                                                                           |
| Telephone/DSL Protection             | No                                                                           |
| <b>PHYSICAL</b>                      |                                                                              |
| Material of Construction             | Plastic                                                                      |
| Power Cord Color                     | Black                                                                        |
| Housing Color                        | Black                                                                        |
| Mounting Holes or Slots              | No                                                                           |
| Receptacle Color                     | Black                                                                        |
| Shipping Dimensions (hwd / in.)      | 3.60 x 6.50 x 5.80                                                           |
| Shipping Dimensions (hwd / cm)       | 9.14 x 16.51 x 14.73                                                         |
| Shipping Weight (lbs.)               | 1.60                                                                         |
| Shipping Weight (kg)                 | 0.73                                                                         |
| Unit Dimensions (hwd / in.)          | 1.420 x 5.210 x 5.210                                                        |
| Unit Dimensions (hwd / cm)           | 3.61 x 13.23 x 13.23                                                         |
| Unit Weight (lbs.)                   | 1.2                                                                          |
| Unit Weight (kg)                     | 0.54                                                                         |
| Input Cord Color                     | Black                                                                        |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                                                                              |
| Rotatable Outlets                    | No                                                                           |
| Antimicrobial                        | No                                                                           |
| GaN Technology                       | No                                                                           |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                                                                              |



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States

|                                                            |                                                                                                                         |
|------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------|
| Product Certifications                                     | CAN/CSA-C22.2 No. 269.3 (Canada); cUL Listed; NOM (Mexico); UL 1449; UL Listed                                          |
| Product Compliance                                         | RoHS                                                                                                                    |
| WARRANTY & SUPPORT                                         |                                                                                                                         |
| Product Warranty Period (Worldwide)                        | Lifetime limited warranty                                                                                               |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$50,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a> |



© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.