**Part Number :** 1731120666
**Product Description :** FCT DIN Coaxial Contact, Female, Right-Angle, Solder Cable Termination, 50 Ohms, 1.30µm Gold Plating, for RG-316U Double Shielded Cable
**Series Number :** 173112
**Status :** Active
**Product Category :** D-Sub Contacts
**Engineering Part Number :** FDX022S102



## Documents and Resources

### Drawings

1731120666_sd.pdf

STEP AP242

SOLIDWORKS

Creo

### Specifications

1731120009-PK-000.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21 |
| REACH SVHC | Contains Lead per D(2022)9120-DC (17 Jan 2023) |
| EU RoHS | Compliant with Exemption 6(c) per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | D-Sub Contacts |
| Series | 173112 |
| Description | FCT DIN Coaxial Contact, Female, Right-Angle, Solder Cable Termination, 50 Ohms, 1.30µm Gold Plating, for RG-316U Double Shielded Cable |
| Contact Type | Coaxial |
| Magnetic | Yes |
| Product Name | FCT Products |
| Type | Mixed Layout |
| UPC | 191128757232 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 2.0A |
| Impedance | 50Ω |

### Physical

| | |
|---|---|
| Durability (mating cycles min) | 500 |
| Gender | Female |
| Material - Contact | Copper Alloy |
| Material - Plating Mating | Gold over Nickel |
| Material - Plating Termination | Gold over Nickel |

Downloaded from Arrow.com.

| | |
|---|---|
| Net Weight | 2.900/g |
| Orientation | Right Angle |
| Packaging Type | Bag |
| Plating min - Mating | 1.300µm |
| Plating min - Termination | 0.200µm |
| Temperature Range - Operating | -55° to +135°C |
| Termination Style | Solder |
| Wire/Cable Type | RG-316U Double Braided |

## Mates With / Use With

### Use with Part(s)

| Description | Part Number |
|---|---|
| Use With | FCT Mixed Layout Connectors |

## Application Tooling

## Global

| Description | Part Number |
|---|---|
| FCT Removal Tool for Size 8 Contacts | 1731121747 |



Downloaded from Arrow.com.