






DESCRIPTION	WIRE SIZE	HYDRAULIC TOOLING 69120- [],314979, 122271- 1		PNEUMATIC TOOLING			TAPE TOOLING			HEAVY HEAD HAND TOOL
		Dies for 69051 59974- 1	Dies for 69066 58422- 1	Heads for 626	Heads for 69015	Jaws for 68068- []	Dies for 68250- 1	Dies for 68354- 1	Dies for 69875	
Terminal/Splice Color Code Red Blue Yellow PLASTI-GRIP* Terminals 	8	48752-1 47820	48858-1 47236-1†	217942-1 L		68229-1	68247-1●	68355-1	68116-1▲	69959
	6	48753-1 47821●	48859-1 47237-1†		68325-1	68233-1	68248-1●			
	4	48754-1 47822●	48860-1 47238-1†		314991-1		68249-1●			
	2	48755-1 47823●	48861-1 47239-1†							
	1/0		48756-1 47824● 47378-1†							
	2/0		48757-1 47825●							
	3/0		48758-1 47915●							
	4/0		48759-1 47918●							
AMPLI-BOND* Terminals 	8	48752-1	48858-1 47236-1†	217942-1 L				68355-1	68116-1▲	69959
	6	48753-1	48859-1 47237-1†		68325-1					
	4	48754-1	48860-1 47238-1†		314991-1					
	2	48755-1	48861-1 47239-1†							
	1/0		48756-1 47378-1†							
	2/0		48757-1							
	3/0		48758-1							
	4/0		48759-1							
TERMINYL* Terminals and Splices 	8	47820●					68247-1●			
	6	47821●					68248-1●			
	4	47822●					68249-1●			
	2	47823●								
	1/0		47824●							
	2/0		47825●							
	3/0		47915●							
	4/0		47918●							
Pre-Insulated Nylon H.D. 	4		69463●							


● No insulation crimp
† Large expansion
▲ Foot pedal operation only

TOOLING AND ACCESSORIES

Hydraulic



Tape Machines



Pneumatic

Hand Tool

