



**Part Number :** [1122191024](#)  
**Product Description :** Woodhead ArcArrest Plug with Handle, Drawplates, and Cap, Switch-Rated, 30.0A, 480V AC, 3-Pole+Ground, Insulator Keying Position 4, Three Grommets Included  
**Series Number :** 112219  
**Status :** Active  
**Product Category :** Wiring Devices  
**Engineering Number :** ARC30MHDE03



---

## Documents & Resources

**Drawings**  
[Drawing 1122191024\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Wiring Devices
Series	112219
Description	Woodhead ArcArrest Plug with Handle, Drawplates, and Cap, Switch-Rated, 30.0A, 480V AC, 3-Pole+Ground, Insulator Keying Position 4, Three Grommets Included
IP Rating	IP69K
NEMA Configuration	N/A
Product Family	Woodhead ArcArrest Connector System
Product Name	ArcArrest
Specialty	Switch-Rated
Type	Plug
UPC	78172558544

### Agency

UL	E145922
----	---------

### Electrical

Current - Maximum per Contact	30.0A
GFCI	No
Voltage - Maximum	480V AC

### Physical

Cord Grip Body Size	F4 1"
Cord Type	N/A
Flange	Yes
Flip Lid	No
Gender	Male
Length	178.99mm (7.047")
Lighted Connector	No

Locking Blade	N/A
Poles	3
Receptacle Type	N/A
Wire Size (AWG)	8 to 12

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Woodhead ArcArrest Receptacle, Switch-Rated, 30.0A, 480V AC, 3-Pole+Ground, Insulator Keying Position 4	<u>1122190010</u>
Woodhead ArcArrest Receptacle with Handle and Drawplates, Switch-Rated, 30.0A, 480V AC, 3-Pole+Ground, Insulator Keying Position 4, Three Grommets Included	<u>1122190024</u>
Woodhead ArcArrest Receptacle with Handle, Switch-Rated, 30.0A, 480V AC, 3-Pole+Ground, Insulator Keying Position 4, Three Grommets Included	<u>1122190038</u>
Woodhead ArcArrest 70° Angle Receptacle, Switch-Rated, 30.0A, 480V AC, 3-Pole+Ground, Insulator Keying Position 4	<u>1122190052</u>

---

This document was generated on Sep 04, 2023