

M12 K-cod 4+PE st/- f/- PUR 5,0m



Image is for illustration purposes only. Please refer to product description.

Part number	21 34 330 0544 050
Specification	M12 K-cod 4+PE st/- f/- PUR 5,0m
HARTING eCatalogue	https://harting.com/21343300544050

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M12 K-coding Female Straight
Type of cable	Copper cable (round)

Version

Cable length	5 m
Number of cores	5
Core structure	5x 1.5 mm ²
Coding	K-coding

Technical characteristics

Rated current	12 A
Rated voltage	600 V AC
Limiting temperature	-25 ... +80 °C
Cable diameter	8.2 mm

Material properties

Material (cable)	PUR (polyurethane)
------------------	--------------------



Pushing Performance
Since 1945

Material properties

Colour (cable)	Black
----------------	-------

Specifications and approvals

Approvals	CE
-----------	----

Commercial data

Packaging size	1
Net weight	615 g
Country of origin	Germany
European customs tariff number	85444290
GTIN	5713140567726
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600