

Johanson Part Number 2450FM07B0037001T

Johanson Part Number: 2450FM07B0037001T

Johanson Company: JTI

Legacy P/N: 2450FM07B0037T

Size for Capacitors (EIA): None

Description: Matched Filters, 402, 2400-2500MHz,
3W, 0.8dB, Ni/Sn (RoHS), Miniature 2.4GHz
Impedance Matched FCC / ETSI Compliant Low
Pass Filter: Optimized for Nordic Semico, 7" Reel
Paper Tape

Specification Number: None

Life Cycle Stage: Active - Production

NCNR: No

AEC Q200 Qualified: No

Thickness (Max): 0.016

Schedule B: 8534.00.00.85

Thickness (Min): None

ITAR: No

End Band(Min): 0.00

ECCN: EAR99

End Band (max): 0.011

RoHS Compliance: Yes, RoHS 10/10

Standard Item: Yes

REACH: Yes

Lead Time Typical (Weeks)*: 14

Country of Origin: TW

Length (Min): 0.037

Product Family: Integrated Passive Components

Length (Max): 0.041

Product Subfamily: Matched Filters

Width (Min):0.018

Capacitance Value: None

Width (Max): 0.022

Cap Unit of Meas: None

Part Weight (mg): None

Tolerance: None

Packaged Width (lb) Arm: None

Voltage: None

Packaging: 7" Reel Paper Tape

Dielectric Temp Coefficient: None

Packaging Qty: 10000

Termination: 0

Operating Temp Range: -40°C to +85°C

Marking: Special

Storage Temp Range (Packaged): -40°C to +85°C

Product Release Date: July 13, 2020, 7 a.m.

Storage Temp Range (None Operating): +5°C to
+35°C with RH 45% to 75%

Harmonization: 8534.00.00.85

*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes.

Web Page Link: <https://www.johansontechnology.com/low-pass-filters>

Printed from: www.johansontechnology.com/search/pn-detail/2450FM07B0037001T/