OMRON Industrial Automation



R89F-DS1225H

DC Axial fan, plastic blade, frame 120x25, high speed

Downloaded from Arrow.com.

Specifications

Size	120 x 120 x 25 mm
Operating voltage at DC	20.4-27.6 V
Rated current	0.47 A
Rated power	11.28 VA
Rated rotational speed	4100 r/min
Maximum flow rate	3.68 m³/min
Maximum static pressure	120 Pa
Noise emission	51 dB(A)
Set content	Fan only

Downloads

CAD Library



R89F

Datasheet

EN PDF 5.37 MB



R89F Axial Fans

Brochure

EN PDF 5.68 MB

TERMS OF WEBSITE USE

This PDF document was created from the European OMRON Industrial Automation website on 26 July, 2026. Click here for terms of use.

OMRON

INDUSTRIAL AUTOMATION | INDUSTRIAL.OMRON.EU

Downloaded from Arrow.com.