

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300680104

Status:

Active

Overview:

BradPower Cordsets and Receptacles

Description:

BradPower D-Size (1 3/8"–M35) 3-Pole Trunk Tee, with 3-Pole BradPower D-Size (1 3/8"–M35) Drop, Red



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E258922
General	
Product Family	Industrial Tees and Splitters
Series	130068
IP Rating	IP67
Overview	BradPower Cordsets and Receptacles
Product Name	BradPower D-Size
Taxonomy	Industrial Tees and Splitters
Type	Power Tap Tee
UPC	78172545166
Physical	
Drop Connector	BradPower D-Size (1 3/8"–M35)
Drop Gender	Female
Keyway	Single
Left Trunk Connector	BradPower D-Size (1 3/8"–M35)
Left Trunk Gender	Female
Leg 1 Length	N/A
Leg 2 Length	N/A
Material - Cable Jacket	N/A
Material - Connector Body	PVC
Material - Coupling Nut	Anodized Aluminum
Net Weight	286.670/g
Poles	3
Right Trunk Connector	BradPower D-Size (1 3/8"–M35)
Right Trunk Gender	Male
Temperature Range - Operating	-20°C to +90°C
Electrical	
Current - Maximum per Contact	32.0A
Voltage - Maximum	600V AC/DC
Material Info	
Engineering Number	TC30C30-200E
Reference - Drawing Numbers	
Sales Drawing	SD-130068-020-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained
ZZCERT_CE - Declaration of Conformity	CER_4000383479_00_000.pdf
ZZCERT_UKCA - Declaration of Conformity	CER_4000410546_00_000.pdf

Search Parts in this Series

130068 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION