Part Number : 2177971033
Product Description : KK 254-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 2.54mm Pitch, Single Row, 600.00mm Length, 3 Circuits, Natural
Series Number : 217797
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents and Resources

Drawings

2177971033_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	217797
Description	KK 254-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 2.54mm Pitch, Single Row, 600.00mm Length, 3 Circuits, Natural
Assembly Configuration	Dual Ended Connectors
Connector to Connector	KK 254-to-Pigtail
Product Name	KK 254
Type	Discrete Wire Assembly
UPC	195842123038

Physical

Cable Length	600.00mm
Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Natural (White)
Gender	Female-Pigtail
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	8.151/g
Number of Rows	1
Pitch - Mating Interface	2.54mm

Downloaded from Arrow.com.

Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 11028
Wire Size (AWG)	22

Mates With / Use With

Mates with Part(s)

Description	Part Number
KK 254 Vertical Breakaway Headers with Friction Lock	42375
KK 254 Right-Angle Surface Mount Compatible Breakaway Headers	42377
KK 254 Right-Angle Breakaway Headers	42376
KK 254 Single Row Vertical Headers	4030
KK 254 Vertical Single Row Solid Headers	6373
KK 254 Vertical Single Row Headers	6410
KK 254 RPC Vertical Headers with Friction Lock	171856
KK 254 RPC Right-Angle Headers with Friction Lock	171857

Downloaded from Arrow.com.