Part Number : 192150030
Product Description : VersaKrimp Butt Splice for 12-10 AWG Wire, Tape and Reel
Series Number : 19215
Status : Active
Product Category : Splices
Engineering Part Number : CS-346T



Documents and Resources

Drawings

192150030_sd.pdf

Specifications

PS-19902-015-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Splices
Series	19215
Description	VersaKrimp Butt Splice for 12-10 AWG Wire, Tape and Reel
Product Name	VersaKrimp
Style	Standard
Type	Butt Splice
UPC	800753053939

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	2.464/g
Packaging Type	Adhesive Tape on Reel
Wire Size (AWG)	10, 12

Application Tooling

Global

Downloaded from Arrow.com.

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	190270088
Mini-Mac Applicator	638851000

Downloaded from Arrow.com.