

Search within category

GO

BUY NOW

DESIGN / INSTALL



STP28X0.2MBU

Category 6A Performance, 28AWG, F/UTP Patch Cord, CM/LSZH, Blue, 0.2m.

Specs	Packaging Details	Documents	★ Add to Favorites	🛒 Add to BOM
Conductor Gauge (AWG)	28			
Performance Level	Category 6A			
Connector 2 Type	RJ45 8(8)			
Connector 1 Type	RJ45 8(8)			
Overall Length (ft.)	0.66			
Overall Length (m)	0.2			
Maximum Operating Temperature (°C)	75			
Maximum Operating Temperature (°F)	167			
Minimum Operating Temperature (°C)	-10			
Minimum Operating Temperature (°F)	14			
Maximum Storage Temperature (°C)	70			
Maximum Storage Temperature (°F)	158			
Minimum Storage Temperature (°C)	-40			
Minimum Storage Temperature (°F)	-40			
Flammability Rating	CM, LSZH-1 (60332-1)			
Standards Met	IEEE 802.3af, 802.3at, 802.3bt type 3 and type 4, UL 1863.			
Cable Color	Blue			
Length (ft.)	0.66			
Termination End 1	Modular Plug			
Termination End 2	Modular Plug			
CE Compliant	Yes			
Nominal Cable Outside Diameter (In.)	0.19			
Nominal Cable Outside Diameter (mm)	4.7			
UL5A Listed	No			
Application	Shielded			
Cable Length (ft.)	0.656			
Cable Length (m)	0.2			

Cable Type	F/UTP
Conductor Material	Copper
Maximum Installation Temperature (°C)	70
Maximum Installation Temperature (°F)	158
Minimum Installation Temperature (°C)	70
Minimum Installation Temperature (°F)	-40
RoHS Compliancy Status	Compliant
Min. Order Qty.	1

[LEGAL INFORMATION](#) | [PRIVACY POLICY](#) | [CONTACT US](#) | [SITE MAP](#) | [WHERE TO BUY](#) | [JOBS](#) | [UNSUBSCRIBE](#)