
HEX40-AB-90-13-A3-1 Product Details



HEX40-AB-90-13-A3-1

TE Internal Number: 892583-000

Active

HexaShield Adapters and Ferrule Kits

Not EU RoHS or ELV Compliant

Product Highlights:

- Connector Code = 40
- Aluminum Alloy Material
- Cadmium Plating over Electroless Nickel Finish
- 90°
- Shell Size = 13, C

View all Features

Add to My Part List | Request Sample | Find Similar Products | Buy Product

Quick Links

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Documentation & Additional Information

Product Drawings:
- HexaShield Adaptor for Code 40 Connector O/NO B 11 E... (PDF, English)

Catalog Pages/Data Sheets:
- None Available

Product Specifications:
- None Available

Application Specifications:
- None Available

Instruction Sheets:
- None Available

CAD Files:
- None Available

List all Documents

Related Products:
- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:
- Material = Aluminum Alloy
- Finish = Cadmium Plating over Electroless Nickel
- Angle = 90°
- Shell Size = 13, C
- Color = Olive Drab

Electrical Characteristics:
- Number of Ferrules = 3
- Overbraid Termination = No Overbraid
- Star Style = Standard
- Recommended Boot = 202K153-25-G03-0

Body Features:
- Connector Code = 40
- Length of Adapter = Standard

Configuration Features:
- Braid = None
- Number of 22 AWG Shielded Pairs, Max. = 12
- Number of 20 AWG Shielded Pairs, Max. = 9

Industry Standards:
- RoHS/ELV Compliance = Not ELV/RoHS compliant
- Lead Free Solder Processes = Not relevant for lead free process

Conditions for Usage:
- Salt Spray Resistance (Hr) = 500

Other:
- Brand = Raychem

© 2012 Tyco Electronics Corporation, a TE Connectivity Ltd. company. All Rights Reserved | Privacy Policy

Provide Website Feedback

Downloaded from Arrow.com.