

# Cable connector - CA-12P1N8AT008S



1619354

<https://www.phoenixcontact.com/us/products/1619354>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

M23, Cable connector, CA, angled, shielded: yes, SPEEDCON locking, No. of pos.: 12, Direction of rotation: Standard, type of contact: Pin, Crimp connection, cable diameter range: 10 mm ... 14.5 mm, coding:N Alternative product in accordance with RoHS II without Exemption 6c (Pb <0.1%) 1243475



## Your advantages

- Angled cable outlet for confined spaces
- Can be adapted to various applications, thanks to adjustable cable outlet direction
- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Reduced connection time with SPEEDCON fast locking system
- Crimping connection: vibration- and temperature-resistant assembly

## Commercial Data

Item number	1619354
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to Order (non-returnable)
Sales Key	A12
Product Key	ABRBFH
Catalog Page	Page 90 (C-2-2019)
GTIN	4046356824903
Weight per Piece (including packing)	186.6 g
Weight per Piece (excluding packing)	186.6 g
Customs tariff number	85366990
Country of origin	DE

# Cable connector - CA-12P1N8AT008S



1619354

<https://www.phoenixcontact.com/us/products/1619354>

## Technical Data

### Notes

Order information:	Order 12 x 1 mm crimp contacts separately
--------------------	---

### Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

### Connector

#### Insulating body

Note	Order information: Order crimp contacts Ø 1 mm separately
Coding	N
Insulation body material	PA 6.6
Connection method	Crimp connection
Contact type	Pin
Application	Signal
Number of positions	12
Direction of rotation	Standard
Connection profile	12
Contact diameter	1 mm
Litz wire cross-section	Signal contacts min. 0.08 mm <sup>2</sup>
Litz wire cross-section	Signal contacts max. 1 mm <sup>2</sup>
Nominal current per signal contact	8 A
Rated voltage Signal contact	48 V AC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

#### Housing

Housing material	Metal
Type of locking	SPEEDCON locking
Pg screw connection	none
Degree of protection (plugged in)	IP67
Thread type	M23

#### Seal

External cable diameter	10 mm ... 14.5 mm
Seal material	NBR

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

# Cable connector - CA-12P1N8AT008S


1619354

<https://www.phoenixcontact.com/us/products/1619354>



## Drawings

Dimensional drawing




# Cable connector - CA-12P1N8AT008S

1619354

<https://www.phoenixcontact.com/us/products/1619354>



Schematic diagram



# Cable connector - CA-12P1N8AT008S



1619354

<https://www.phoenixcontact.com/us/products/1619354>

## Approvals

cUL Recognized Approval ID: E335019-20141210				
	Nominal Voltage $U_N$	Nominal Current $I_N$	Cross Section AWG	Cross Section $\text{mm}^2$
	48 V	4 A	- 20	-

UL Recognized Approval ID: E335019-20141210				
	Nominal Voltage $U_N$	Nominal Current $I_N$	Cross Section AWG	Cross Section $\text{mm}^2$
	48 V	6 A	- 20	-

cULus Recognized				
------------------	--	--	--	--

# Cable connector - CA-12P1N8AT008S



1619354

<https://www.phoenixcontact.com/us/products/1619354>

## Classifications

### ECLASS

ECLASS-9.0	27440102
ECLASS-10.0.1	27440102
ECLASS-11.0	27440102

### ETIM

ETIM 8.0	EC002635
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# Cable connector - CA-12P1N8AT008S



1619354

<https://www.phoenixcontact.com/us/products/1619354>

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

# Cable connector - CA-12P1N8AT008S

1619354

<https://www.phoenixcontact.com/us/products/1619354>



## Accessories

### Torque screwdriver

Torque screwdriver - SF-Z0028 - 1607456

<https://www.phoenixcontact.com/us/products/1607456>

Torque screwdriver, series: RC



### Hook wrench

Hook wrench - SF-Z0027 - 1607455

<https://www.phoenixcontact.com/us/products/1607455>

Hook wrench, series: RC





# Cable connector - CA-12P1N8AT008S



1619354

<https://www.phoenixcontact.com/us/products/1619354>

## Protective cap

Protective cap - RC-Z2058 - 1604223

<https://www.phoenixcontact.com/us/products/1604223>

Plastic protection cap for connectors with M23 knurled nut



---

## Plastic anti-static dust protection cap

Plastic anti-static dust protection cap - RC-Z2468 - 1611796

<https://www.phoenixcontact.com/us/products/1611796>

Plastic protection cap, antistatic, for connectors with M23 knurled nut



# Cable connector - CA-12P1N8AT008S



1619354

<https://www.phoenixcontact.com/us/products/1619354>

## Color-coding

Color-coding - RF-Z0014 - 1620588

<https://www.phoenixcontact.com/us/products/1620588>

Color-coding, color: green



---

## Color-coding

Color-coding - RF-Z0015 - 1620592

<https://www.phoenixcontact.com/us/products/1620592>

Color-coding, color: orange



# Cable connector - CA-12P1N8AT008S



1619354

<https://www.phoenixcontact.com/us/products/1619354>

## Color-coding

Color-coding - RF-Z0016 - 1620593

<https://www.phoenixcontact.com/us/products/1620593>

Color-coding, color: black



---

## Crimp contact

Crimp contact - RC-11P2000 - 1596770

<https://www.phoenixcontact.com/us/products/1596770>



Crimp contact, turned, Single contact, contact diameter: 1 mm, crimp range: 0.08 mm<sup>2</sup> ... 0.22 mm<sup>2</sup>, Alternative product in accordance with RoHS II without Exemption 6c (Pb <0.1%) 1240882

# Cable connector - CA-12P1N8AT008S



1619354

<https://www.phoenixcontact.com/us/products/1619354>

## Crimp contact

Crimp contact - RC-12P2000 - 1597862

<https://www.phoenixcontact.com/us/products/1597862>



Crimp contact, turned, Single contact, contact diameter: 1 mm, crimp range: 0.14 mm<sup>2</sup> ... 0.56 mm<sup>2</sup>, Alternative product in accordance with RoHS II without Exemption 6c (Pb <0.1%) 1240882

---

## Crimp contact

Crimp contact - RC-1KP2000 - 1602996

<https://www.phoenixcontact.com/us/products/1602996>



Crimp contact, turned, Single contact, contact diameter: 1 mm, crimp range: 0.5 mm<sup>2</sup> ... 1 mm<sup>2</sup>

# Cable connector - CA-12P1N8AT008S



1619354

<https://www.phoenixcontact.com/us/products/1619354>

## Crimp contact

Crimp contact - RC-22P2000 - 1603321

<https://www.phoenixcontact.com/us/products/1603321>



Crimp contact, rolled, Single contact, contact diameter: 1 mm, crimp range: 0.22 mm<sup>2</sup> ... 0.56 mm<sup>2</sup>, Single contact

## Crimp contact

Crimp contact - RC-22P2300 - 1603324

<https://www.phoenixcontact.com/us/products/1603324>



Crimp contact, rolled, Taped articles, number of pieces per reel: 500, contact diameter: 1 mm, crimp range: 0.22 mm<sup>2</sup> ... 0.56 mm<sup>2</sup>

# Cable connector - CA-12P1N8AT008S



1619354

<https://www.phoenixcontact.com/us/products/1619354>

## Crimp contact

Crimp contact - RC-22P2400 - 1603325

<https://www.phoenixcontact.com/us/products/1603325>



Crimp contact, rolled, number of pieces per reel: 10000, contact diameter: 1 mm, crimp range: 0.22 mm<sup>2</sup> ... 0.56 mm<sup>2</sup>

---

## Crimp contact

Crimp contact - RC-21P2000 - 1603310

<https://www.phoenixcontact.com/us/products/1603310>



Crimp contact, rolled, Single contact, contact diameter: 1 mm, crimp range: 0.08 mm<sup>2</sup> ... 0.22 mm<sup>2</sup>, Single contact

# Cable connector - CA-12P1N8AT008S



1619354

<https://www.phoenixcontact.com/us/products/1619354>

## Crimp contact

Crimp contact - RC-21P2300 - 1603313

<https://www.phoenixcontact.com/us/products/1603313>



Crimp contact, rolled, Taped articles, number of pieces per reel: 500, contact diameter: 1 mm, crimp range: 0.08 mm<sup>2</sup> ... 0.22 mm<sup>2</sup>

## Crimp contact

Crimp contact - RC-21P2400 - 1611637

<https://www.phoenixcontact.com/us/products/1611637>



Crimp contact, rolled, number of pieces per reel: 10000, contact diameter: 1 mm, crimp range: 0.08 mm<sup>2</sup> ... 0.22 mm<sup>2</sup>

Phoenix Contact 2022 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)