

VS-PPC-C1-RJ45-POBK-8I10G - RJ45 connector



1422205

<https://www.phoenixcontact.com/us/products/1422205>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



RJ45 connector, degree of protection: IP65/IP67, number of positions: 8, 10 Gbps, CAT6_A, material: Plastic, connection method: Crimp connection, connection cross section: AWG 27- 24, cable outlet: straight, color: black, Ethernet

Commercial Data

Item number	1422205
Packing unit	1 pc
Minimum order quantity	1 pc
Sales Key	AB12
Product Key	ABNEAA
Catalog Page	Page 358 (C-2-2019)
GTIN	4046356571999
Weight per Piece (including packing)	30.4 g
Weight per Piece (excluding packing)	29.6 g
Customs tariff number	85366990
Country of origin	DE

VS-PPC-C1-RJ45-POBK-8I10G - RJ45 connector



1422205

<https://www.phoenixcontact.com/us/products/1422205>

Technical Data

Product properties

Type	RJ45
Product type	Data plug
Number of positions	8
Connection profile	RJ45
No. of cable outlets	1
Locking type	Push Pull
Shielded	yes
Cable outlet	straight

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Electrical properties

Rated voltage (III/3)	72 V (DC)
Rated current	1 A
Nominal voltage U_N	48 V
Nominal current I_N	1 A
Transmission medium	Copper

Dimensions

Width	22 mm
Height	30 mm
Length	57.7 mm

Material specifications

Color	black
Housing material	Plastic

Cable/line

Shielded	yes
External cable diameter	5 mm ... 8 mm
Conductor cross section	0.14 mm ²

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 200
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

VS-PPC-C1-RJ45-POBK-8I10G - RJ45 connector



1422205

<https://www.phoenixcontact.com/us/products/1422205>

Degree of protection	IP65/IP67
Ambient temperature (operation)	-25 °C ... 60 °C

Standards and regulations

Standards/specifications	IEC PAS 61076-3-117
--------------------------	---------------------

VS-PPC-C1-RJ45-POBK-8I10G - RJ45 connector

1422205

<https://www.phoenixcontact.com/us/products/1422205>



Approvals



EAC

Approval ID: B.01687

VS-PPC-C1-RJ45-POBK-8I10G - RJ45 connector



1422205

<https://www.phoenixcontact.com/us/products/1422205>

Classifications

ECLASS

ECLASS-11.0	27440101
ECLASS-12.0	27440113
ECLASS-13.0	27440113

ETIM

ETIM 8.0	EC002636
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VS-PPC-C1-RJ45-POBK-8I10G - RJ45 connector



1422205

<https://www.phoenixcontact.com/us/products/1422205>

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

VS-PPC-C1-RJ45-POBK-8I10G - RJ45 connector

1422205

<https://www.phoenixcontact.com/us/products/1422205>



Accessories

VS-CABLE-STRIP-VARIO - Stripping tool

1657407

<https://www.phoenixcontact.com/us/products/1657407>

Stripping tool, for the multi-level stripping of shielded cables



Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com