Part Number : 22023083
Product Description : Non-ZIF, Vertical, Low Profile Receptacle, 8 Circuits
Series Number : 5229
Status : Obsolete
Product Category : FFC / FPC Connectors
Engineering Part Number : 5229-08CPB

Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Obsolete

Downloaded from Arrow.com.

Part Details

General

Status	Obsolete
Category	FFC / FPC Connectors
Series	5229
Description	Non-ZIF, Vertical, Low Profile Receptacle, 8 Circuits
Contact Type	N/A
Product Name	Easy-On
UPC	800753593664

Agency

UL	E29179

Electrical

Current - Maximum per Contact	0.5A, 1.0A
Voltage - Maximum	200V

Physical

Actuator Type	Non-ZIF
Circuits (Loaded)	8
Contact Position	N/A
Mated Height	6.50mm
Net Weight	980.200/mg
Orientation	Vertical
Packaging Type	Tray
PCB Mounting	Through Hole
PCB Retention	No
PC Tail Length	3.60mm
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to PCB	No
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire/Cable Type	FFC/FPC

Obsolete

Downloaded from Arrow.com.

This document was generated on Sep 22, 2026

Obsolete

Downloaded from Arrow.com.