



Part Number : [986581212](#)

Product Description : MOX Crimp Terminal, Female, 0.635mm, 18-22 AWG (0.75mm²), Reel, Tin (Sn)

Series Number : 98658

Status : Active

Product Category : Crimp Terminals

Documents & Resources

Drawings

[Drawing 986581212_sd.pdf](#)

3D Models and Design Files

[3D Model 986581212_stp.zip](#)

Specifications

[Application Specification AS-98658-001-001.pdf](#)

[Application Specification AS-98658-001-CH-001.pdf](#)

[Application Specification AS-98944-005-001.pdf](#)

[Application Specification 989820002-AS-000.pdf](#)


[Application Specification 989820002-AS-CH-000.pdf](#)

Tooling Specifications

[Crimp Specification CS-98658-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Duty-To-Declare
China RoHS	
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Terminals
Series	98658
Description	MOX Crimp Terminal, Female, 0.635mm, 18-22 AWG (0.75mm ²), Reel, Tin (Sn)
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Terminal has Stainless Steel Sleeve
Product Family	MOX Products
Product Name	MOX
UPC	800756560199

Electrical

Current - Maximum per Contact	7.5A
-------------------------------	------

Physical

Durability (mating cycles max)	20
Gender	Female
Material - Metal	Copper-Nickel-Silicon, Stainless Steel
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.258/g
Packaging Type	Reel
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Termination Interface Style	Crimp or Compression

Wire Insulation Diameter	1.70mm max.
Wire Size (AWG)	18
Wire Size mm ²	0.82

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Use with Part(s)

Description	Part Number
Use With	All 0.635mm MOX Housings

Application Tooling

Global

Description	Part Number
Hand Crimp Tool	<u>638119300</u>
MOX Extraction Tool	<u>638132600</u>
Extractor Tool for 2.80mm Crimp Terminals	<u>638136900</u>
Extractor Tool for 2.80mm Crimp Terminals	<u>638137000</u>
Extractor Tool for MOX 0.635mm Receptacle Crimp Terminals	<u>638138400</u>
Extractor Tool for MOX 0.635mm Receptacle Crimp Terminals	<u>638138500</u>
Extractor Tool for MOX 0.635mm Receptacle Crimp Terminals	<u>638244400</u>
FineAdjust Applicator	<u>638667000</u>

This document was generated on Jul 31, 2024