



+ TERMINALS & SPLICES

SPLICES



✓ Active

TE CONNECTIVITY (TE)

D-609-11

Raychem

680331-000
TE Internal Number: 680331-000
Alias ID: 7-1195350-8

Not Yet Reviewed for EU RoHS
Not Yet Reviewed for EU ELV

Product Type Splice System Crimp

Terminal & Splice Style Splice

Wire Size (AWG) 16 – 12

Wire Size (mm²) .95 – 3.37

Wire Size (CMA) 1900 – 6755

↓ PRODUCT DRAWING
English

DOCUMENTATION

Product Drawings

Color Coded Crimp Splicer, In-Line, Nickel Plated

PDF
English

Catalog Pages/Data Sheets

1654025_Sec8_D-436

PDF
English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Product Type Splice System Crimp
Splice Type Butt Splice

Contact Features

Terminal & Splice Style Splice

Dimensions

Wire Size (AWG) 16 – 12
Wire Size (mm²) .95 – 3.37
Wire Size (CMA) 1900 – 6755

Usage Conditions

Operating Temperature Range (°C) 200

Industry Standards

Government Qualified No

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance
PDF