






NOTES :
1. THE PRODUCT (LF) MEETS EUROPEAN UNION DIRECTIVES AND
OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-47-004

ORDERING INFORMATION



TECHNICAL SPECIFICATION

INSULATOR MATERIAL : SELF EXTINGUISHING THERMOPLASTIC (UL94 VO)
CONTACT MATERIAL : COPPER ALLOY
MAXIMUM VOLTAGE : 500 V rms.
NOMINAL CURRENT : 3A AT 20°C
INSULATION RESISTANCE : > 1000 MΩ
CLIMATIC CATAGORY : -55°C TO +125°C / 21 DAYS EXPOSURE TO-
INDUSTRIAL ENVIRONMENT HUMIDITY TEST AS HE-14.
CONTACT RESISTANCE : < 20mΩ

mat'l. code REF TECH SPEC				surface ISO 1302 ✓				tolerance ISO 406 ISO 1101				projection 				product family 8614																	
ltr	ecn no		dr	date		tolerances unless otherwise specified								title FEMALE SHORTING PLUG (CLOSED)																			
C	I06-0124		MKV	2002-07-12		angles		linear		.0±0.1																				MM 			
D	I06-0126		MKV	2003-06-07																													
E	I06-0127		MKV	2004-09-29		0°±1°																								scale —			
F	I06-0116		AB	2006-07-20		dr	MINI K VANDANATH				1998-12-06								dwg no				sheet 1 of 1				size						
G	ELX-I-19435		GMA	2014-11-15		engr	JAI.K.A				1998-12-06								C-8614-0085				A3										
H	ELX-I-24519		GMA	2016-07-15		chr	GREGAR.M				2016-07-15																						
						appd	BIJU K P				2016-07-15																						
sheet index		revision		C	D	E	F	G	H																								
		sheet		1	1	1	1	1	1																								