



All Products

Search by part # or keyword



Login/Register
My Account



Cart

- Products
- Industries
- Services & Trainings
- Tools & Resources
- About TE
- Sustainability
- Shop TE Store

Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors

2204416-3 ACTIVE

Rectangular Power Connectors, Header, Receptacle, Board-to-Board, 26 Position, 5 mm [.196 in] Centerline, Printed Circuit Board, MULTI-BEAM HD



MULTI-BEAM | MULTI-BEAM HD

TE Internal #: 2204416-3
TE Internal Description: MB HD R/A.REC.2P+2LP+2P+20S SOLDER

Rectangular Power Connector Type : **Header**
Connector & Housing Type : **Receptacle**
Connector System : **Board-to-Board**
Number of Positions : **26**
Centerline (Pitch) : **5 mm [.196 in]**

Add to List | Similar Products | Digital Datasheet

GET FREE SAMPLES

Compatible Parts & Tooling

Documents

Features

Product Compliance

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features	Rectangular Power Connector Type : Header Connector & Housing Type : Receptacle Connector System : Board-to-Board Sealable : No Connector & Contact Terminates To : Printed Circuit Board
Configuration Features	Number of Positions : 26 PCB Mount Orientation : Right Angle Number of Power Positions : 6 Number of Signal Positions : 20 Number of Rows : 5 Number of Positions by Circuit Application : 4P/Power, 2LP/Lower Power, 20/Signal
Electrical Characteristics	Operating Voltage (VAC): 60 Operating Voltage (VDC): 60
Contact Features	Contact Underplating Material : Nickel Contact Mating Area Plating Material : Gold Flash over Palladium Nickel Contact Current Rating (Max) (A): 93 Contact Retention Within Housing : Without Contact Type : Receptacle PCB Contact Termination Area Plating Material : Tin Contact Mating Area Plating Material Thickness : .076 µm [3 µin]
Termination Features	Termination Post & Tail Length (mm): 3.2 Termination Method to Printed Circuit Board : Through Hole - Solder
Mechanical Attachment	Connector Mounting Type : Board Mount
Housing Features	Centerline (Pitch) : 5 mm [.196 in] Housing Color : Black Housing Material : High Temperature Thermoplastic
Dimensions	Row-to-Row Spacing : 2 mm [.079 in]
Usage Conditions	Operating Temperature Range : -40 – 125 °C [-40 – 257 °F]
Operation/Application	Circuit Application : Power & Signal
Industry Standards	UL Flammability Rating : UL 94V-0 Glow Wire Rating : High Temperature Part - Not Glow Wire
Packaging Features	Packaging Method : Box & Tray

Compatible Parts

All Compatible Parts (2)

Tooling Parts (1)

Associated Parts (1)

ASSOCIATED

2204456-3

Rectangular Power Connectors, Header, Plug, Board-to-Board, 26 Position, 5 mm [.196 in]...

From: \$27.250
In-Stock

VIEW PRODUCT

TOOLING

1-2215067-7

ASSY, EXTRACTION TOOL, 1 X 4

Non-Stocked

VIEW PRODUCT

Products with Similar Specs

[View All Similar Products](#)

THIS PRODUCT

RECTANGULAR POWER CONNECTORS
2204416-3
Rectangular Power Connectors, Header, Receptacle, Board-to-Board...

In-Stock

Rectangular Power Connector Type : **Header**
Connector & Housing Type : **Receptacle**
Connector System : **Board-to-Board**
Number of Positions : **26**
Centerline (Pitch) : **5 mm**

TOP RESULTS

RECTANGULAR POWER CONNECTORS
2204456-3
Rectangular Power Connectors, Header, Plug, Board-to-Board, 26...

In-Stock

Rectangular Power Connector Type : **Header**
Connector & Housing Type : **Plug**
Connector System : **Board-to-Board**
Number of Positions : **26**
Centerline (Pitch) : **5 mm**

RECTANGULAR POWER CONNECTORS
2204400-4
Rectangular Power Connectors, Header, Receptacle, Board-to-Board...

From **\$32.971**
In-Stock

Rectangular Power Connector Type : **Header**
Connector & Housing Type : **Receptacle**
Connector System : **Board-to-Board**
Number of Positions : **36**
Centerline (Pitch) : **5 mm**

RECTANGULAR POWER CONNECTORS
2204426-4
Rectangular Power Connectors, Header, Receptacle, Board-to-Board...

From **\$24.482**
In-Stock

Rectangular Power Connector Type : **Header**
Connector & Housing Type : **Receptacle**
Connector System : **Board-to-Board**
Number of Positions : **17**
Centerline (Pitch) : **5 mm**

Customers Also Bought

TE Part #: **2327677-3**
Internal I/O Connectors, Silver for SFF-TA-1002, PCB...

\$16.074 per unit
Inventory: In-Stock

Add To Cart

Also in the Series | MULTI-BEAM HD

Rectangular Power Connectors (46)

Contact Our Team – 24/7 Support

- +1 800 522 6752
- Live Chat
- See Support Details

Connect With Us



Access Partner Information

- Distributors
- Suppliers
- Supplier Diversity

Get Answers Now

- Authorized Distributors & Resellers
- Product FAQs
- Samples FAQs
- TE Store FAQs
- Terms and Conditions of Sale
- Samples Terms and Conditions

Select Your Preferences

- Language
- English (EN)
- Ship to
- United States (\$USD)