

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0685324462

Status:

Active

Overview:

In-Vehicle Smart Charging Modules

Description:

In-Vehicle Dual Port Smart Charger, USB Type A, with Backlight and Dust Cover, 2.4A



Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Datasheet (PDF)	
General	
Product Family	I/O Connectors
Series	72610
Application	Module-to-Wire
Component Type	USB Charger
Overview	In-Vehicle Smart Charging Modules
Product Name	Mini50, USB
Type	A
UPC	191128149389
Physical	
Circuits (Loaded)	2
Circuits (maximum)	4
Color - Resin	Black
Durability (mating cycles max)	10000
Lock to Mating Part	Yes
Material - Plating Mating	N/A
Material - Resin	ABS, PC
Net Weight	41.779/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	N/A
Polarized to Mating Part	Yes
Ports	2
Temperature Range - Operating	-40° to +85°C
Termination Interface: Style	N/A
Waterproof / Dustproof	No
Electrical	
Current - Maximum per Contact	2.4A
Material Info	
Reference - Drawing Numbers	
Sales Drawing	685324462-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 7(c)-I*	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free Status	
Low-Halogen*	
For more information, please visit Contact US	
CUST_NOTE	*Product contains part(s) with customer managed
CUST_NOTE1	EHS data. These part(s) are excluded from
CUST_NOTE2	product compliance status evaluation.
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained*

Search Parts in this Series
72610 Series

Mates With
USB Type A (Front)
Mini50 Unsealed Receptacle 34791-0040 (Rear)

Use With
16V DC

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION