



|                |     |        |       |     |    |                                                    |              |
|----------------|-----|--------|-------|-----|----|----------------------------------------------------|--------------|
| SAC305         | 245 | 0.6mm  | 58    | Yes |    | 245 58<br>Sn96.5Ag3Cu0.5<br>0.6mm 1/2kg Spl<br>(D) | 40510848     |
| SAC305         | 245 | 0.6mm  | 58    | Yes | No | 245 965A3C05 58<br>060M050 125 W                   | 92-7068-8860 |
| SAC305         | 245 | 0.6mm  | 58    | Yes | No | 245 965A3C05 58<br>060M050 125                     | 92-7068-8860 |
| SAC305         | 245 | 0.6mm  | 66    | Yes | No | 245 965A3C05 66<br>060M050 125                     | 92-7068-9030 |
| SAC305         | 245 | 0.8mm  | 4.50% | Yes | No | 245 965A3C05 45<br>080M050B1 125                   | 92-7068-8832 |
| SAC305         | 245 | 0.8mm  | 58    | Yes |    | 245 58<br>Sn96.5Ag3Cu0.5<br>0.8mm 1/2kg Spl<br>(D) | 40510750     |
| SAC305         | 245 | 0.8mm  | 58    | Yes | No | 245 965A3C05 58<br>080M050 125                     | 92-7068-8801 |
| SAC305         | 245 | 0.8mm  | 66    | Yes | No | 245 965A3C05 66<br>080M050 125                     | 92-7068-9014 |
| SAC305         | 245 | 1.0mm  | 58    | Yes |    | 245 965A3C05 58<br>100M050 125                     | WM2650       |
| SAC305         | 245 | 1.0mm  | 66    | Yes | No | 245 965A3C05 66<br>100M050 125                     | 92-7068-8825 |
| SAC305         | 245 | 1.6mm  | 58    | Yes | No | 245 965A3C05 58<br>160M050 125                     | 92-7068-8803 |
| SAC357         | 245 | 0.25mm | 66    | Yes | No | 245 958A35C07 66<br>025M010 005                    | 90-7059-8810 |
| SAC357         | 245 | 0.4mm  | 58    | Yes | No | 245 958A35C07 58<br>040M025 125                    | 91-7059-8843 |
| SAC357         | 245 | 0.4mm  | 66    | Yes | No | SN95.8AG3.5CU.7<br>#66/245 0.015 250<br>GRAM SPL   | 91-7059-8815 |
| SAC387         | 245 | 0.6mm  | 66    | Yes | No | 245 955A38C07 66<br>060M050 125                    | 92-7058-8842 |
| SN40PB60       | 245 | 0.062  | 50    | No  |    | SN40PB60 #50/245<br>.062 5 LB SPL                  | 2640608817   |
| SN50PB50       | 245 | 0.04   | 50    | No  |    | SN50PB50 #50/245<br>.040 5 LB SPL                  | 2650508813   |
| SN5PB93.5AG1.5 | 245 | 0.031  | 58    | No  |    | SN05PB93.5AG01.5<br>#58/245 .031 1 LB<br>SPL       | 2473408801   |
| SN5PB93.5AG1.5 | 245 | 0.04   | 50    | No  |    | SN05PB93.5AG01.5<br>#50/245 .040 1 LB<br>SPL       | 2473408813   |
| SN60PB40       | 245 | 0.031  | 50    | No  |    | SN60PB40 #50/245<br>.031 1 LB SPL                  | 2460408800   |
| SN60PB40       | 245 | 0.031  | 66    | No  |    | SN60PB40 #66/245<br>.031 1 LB SPL                  | 2460408802   |
| SN60PB40       | 245 | 0.04   | 66    | No  |    | SN60PB40 #66/245<br>.040 1 LB SPL                  | 2460408825   |
| SN60PB40       | 245 | 0.05   | 58    | No  |    | SN60PB40 #58/245<br>.050 1 LB SPL                  | 2460408815   |
| SN60PB40       | 245 | 0.05   | 66    | No  |    | SN60PB40 #66/245<br>.050 1 LB SPL                  | 2460408816   |
| SN60PB40       | 245 | 0.062  | 50    | No  |    | SN60PB40 #50/245<br>.062 1 LB SPL                  | 2460408817   |
| SN60PB40       | 245 | 0.4mm  | 50    | No  |    | 245 50 Sn60Pb40<br>0.4mm 1/4kg Spl<br>(D)          | 40510935     |
| SN60PB40       | 245 | 0.4mm  | 58    | No  | No | 245 6040 58 040M<br>025 125                        | 91-6040-9013 |
| SN60PB40       | 245 | 0.6mm  | 50    | No  |    | 245 50 Sn60Pb40<br>0.6mm 1/2kg Spl<br>(D)          | 40510227     |
| SN60PB40       | 245 | 0.6mm  | 58    | No  | No | 245 6040 58 060M<br>050 125                        | 92-6040-8860 |
| SN60PB40       | 245 | 0.8mm  | 50    | No  |    | 245 50 Sn60Pb40<br>0.8mm 1/2kg Spl<br>(D)          | 40510228     |
| SN60PB40       | 245 | 0.8mm  | 58    | No  | No | 245 6040 58 080M<br>050 125                        | 92-6040-8801 |

|             |     |       |    |    |    |                                           |              |
|-------------|-----|-------|----|----|----|-------------------------------------------|--------------|
| SN60PB40    | 245 | 0.8mm | 60 | No | No | 245 6040 60 080M<br>050B4 005             | 96-6040-8832 |
| SN60PB40    | 245 | 0.8mm | 66 | No |    | 245 66 Sn60Pb40<br>0.8mm 1/2kg Spl        | 40500252     |
| SN60PB40    | 245 | 1.0mm | 50 | No |    | 245 50 Sn60Pb40<br>1.0mm 1/2kg Spl<br>(D) | 40510229     |
| SN60PB40    | 245 | 1.0mm | 58 | No | No | 245 6040 58 100M<br>050 125               | 92-6040-8846 |
| SN60PB40    | 245 | 1.2mm | 50 | No |    | 245 50 Sn60Pb40<br>1.2mm 1/2kg Spl<br>(D) | 40510230     |
| SN60PB40    | 245 | 1.5mm | 50 | No |    | 245 50 Sn60Pb40<br>1.5mm 1/2kg Spl<br>(D) | 40510232     |
| SN62PB36AG2 | 245 | 0.015 | 50 | No |    | SN62PB36AG02<br>#50/245 .015 1 LB<br>SPL  | 2471508806   |
| SN62PB36AG2 | 245 | 0.02  | 58 | No |    | SN62PB36AG02<br>#58/245 .020 1 LB<br>SPL  | 2471508834   |
| SN62PB36AG2 | 245 | 0.02  | 66 | No |    | SN62PB36AG02<br>#66/245 .020 3 LB<br>SPL  | 2971508808   |
| SN62PB36AG2 | 245 | 0.025 | 50 | No |    | SN62PB36AG02<br>#50/245 .025 1 LB<br>SPL  | 2471508809   |
| SN62PB36AG2 | 245 | 0.025 | 66 | No |    | SN62PB36AG02<br>#66/245 .025 1 LB<br>SPL  | 2471508842   |
| SN62PB36AG2 | 245 | 0.031 | 50 | No |    | SN62PB36AG02<br>#50/245 .031 1 LB<br>SPL  | 2471508800   |
| SN62PB36AG2 | 245 | 0.031 | 58 | No |    | SN62PB36AG02<br>#58/245 .031 1 LB<br>SPL  | 2471508801   |
| SN62PB36AG2 | 245 | 0.031 | 66 | No |    | SN62PB36AG02<br>#66/245 .031 2 LB<br>SPL  | 2271508802   |
| SN62PB36AG2 | 245 | 0.031 | 66 | No |    | SN62PB36AG02<br>#66/245 .031 1 LB<br>SPL  | 2471508802   |
| Sn62Pb36Ag2 | 245 | 0.4mm | 50 | No | No | 245 50<br>Sn62Pb36Ag2<br>0.4mm 1/2kg Spl  | 40500040     |
| Sn62Pb36Ag2 | 245 | 0.6mm | 50 | No | No | 245 50<br>Sn62Pb36Ag2<br>0.6mm 1lb Spl    | 40500488     |
| Sn62Pb36Ag2 | 245 | 0.8mm | 50 | No | No | 245 50<br>Sn62Pb36Ag2<br>0.8mm 1/2kg Spl  | 40500044     |
| SN63PB37    | 245 | 0.01  | 50 | No |    | SN63PB37 #50/245<br>.010 1 LB SPL         | 2463378810   |
| SN63PB37    | 245 | 0.01  | 58 | No |    | SN63PB37 #58/245<br>.010 1 LB SPL         | 2463378850   |
| SN63PB37    | 245 | 0.01  | 66 | No |    | SN63PB37 #66/245<br>.010 1 LB SPL         | 2463378870   |
| SN63PB37    | 245 | 0.015 | 50 | No |    | SN63PB37 #50/245<br>.015 1 LB SPL         | 2463378806   |
| SN63PB37    | 245 | 0.015 | 58 | No |    | SN63PB37 #58/245<br>.015 1 LB SPL         | 2463378843   |
| SN63PB37    | 245 | 0.015 | 66 | No |    | SN63PB37 #66/245<br>.015 1 LB SPL         | 2463378853   |
| SN63PB37    | 245 | 0.02  | 50 | No |    | SN63PB37 #50/245<br>.020 1 LB SPL         | 2463378807   |
| SN63PB37    | 245 | 0.02  | 58 | No |    | SN63PB37 #58/245<br>.020 1 LB SPL         | 2463378834   |
| SN63PB37    | 245 | 0.02  | 66 | No |    | SN63PB37 #66/245<br>.020 1 LB SPL         | 2463378808   |
| SN63PB37    | 245 | 0.025 | 50 | No |    | SN63PB37 #50/245<br>.025 1 LB SPL         | 2463378809   |
| SN63PB37    | 245 | 0.025 | 58 | No |    | SN63PB37 #58/245<br>.025 1 LB SPL         | 2463378860   |

|          |     |        |    |    |    |                                           |              |
|----------|-----|--------|----|----|----|-------------------------------------------|--------------|
| SN63PB37 | 245 | 0.025  | 66 | No |    | SN63PB37 #66/245<br>.025 1 LB SPL         | 2463378842   |
| SN63PB37 | 245 | 0.03   | 50 | No |    | SN63PB37 #50/245<br>.030 1 LB SPL         | 2463378811   |
| SN63PB37 | 245 | 0.031  | 50 | No |    | SN63PB37 #50/245<br>.031 1 LB SPL         | 2463378800   |
| SN63PB37 | 245 | 0.031  | 58 | No |    | SN63PB37 #58/245<br>.031 1 LB SPL         | 2463378801   |
| SN63PB37 | 245 | 0.031  | 66 | No |    | SN63PB37 #66/245<br>.031 1 LB SPL         | 2463378802   |
| SN63PB37 | 245 | 0.04   | 50 | No |    | SN63PB37 #50/245<br>.040 1 LB SPL         | 2463378813   |
| SN63PB37 | 245 | 0.04   | 58 | No |    | SN63PB37 #58/245<br>.040 1 LB SPL         | 2463378846   |
| SN63PB37 | 245 | 0.04   | 66 | No |    | SN63PB37 #66/245<br>.040 1 LB SPL         | 2463378825   |
| SN63PB37 | 245 | 0.05   | 50 | No |    | SN63PB37 #50/245<br>.050 5 LB SPL         | 2663378814   |
| SN63PB37 | 245 | 0.05   | 50 | No |    | SN63PB37 #50/245<br>.050 1 LB SPL         | 2463378814   |
| SN63PB37 | 245 | 0.05   | 66 | No |    | SN63PB37 #66/245<br>.050 1 LB SPL         | 2463378816   |
| SN63PB37 | 245 | 0.062  | 50 | No |    | SN63PB37 #50/245<br>.062 5 LB SPL         | 2663378817   |
| SN63PB37 | 245 | 0.062  | 50 | No |    | SN63PB37 #50/245<br>.062 1 LB SPL         | 2463378817   |
| SN63PB37 | 245 | 0.062  | 58 | No |    | SN63PB37 #58/245<br>.062 1 LB SPL         | 2463378803   |
| SN63PB37 | 245 | 0.062  | 66 | No |    | SN63PB37 #66/245<br>.062 1 LB SPL         | 2463378804   |
| SN63PB37 | 245 | 0.25mm | 58 | No |    | 245 58 Sn63Pb37<br>0.25mm 1lb Spl         | 40500489     |
| SN63PB37 | 245 | 0.25mm | 58 | No |    | 245 58 Sn63Pb37<br>0.25mm 1/4kg Spl       | 40500974     |
| SN63PB37 | 245 | 0.4mm  | 50 | No |    | 245 50 Sn63Pb37<br>0.4mm 1/4kg Spl<br>(D) | 40510003     |
| SN63PB37 | 245 | 0.4mm  | 58 | No |    | 245 58 Sn63Pb37<br>0.4mm 1/4kg Spl<br>(D) | 40510016     |
| SN63PB37 | 245 | 0.4mm  | 58 | No | No | 245 6337 58 040M<br>025 125               | 91-6337-8843 |
| SN63PB37 | 245 | 0.5mm  | 50 | No | No | 245 6337 50 050M<br>025 125               | 91-6337-8807 |
| SN63PB37 | 245 | 0.5mm  | 50 | No | No | 245 6337 50 050M<br>025 125 W             | 91-6337-8807 |
| SN63PB37 | 245 | 0.5mm  | 58 | No | No | 245 6337 58 050M<br>025 125               | 92-6337-8834 |
| SN63PB37 | 245 | 0.5mm  | 58 | No | No | 245 6337 58 050M<br>025 125 W             | 91-6337-8834 |
| SN63PB37 | 245 | 0.6mm  | 50 | No |    | 245 50 Sn63Pb37<br>0.6mm 1/2kg Spl<br>(D) | 40510007     |
| SN63PB37 | 245 | 0.6mm  | 50 | No | No | 245 6337 50 060M<br>050 125               | 92-6337-8809 |
| SN63PB37 | 245 | 0.6mm  | 50 | No | No | 245 6337 50 060M<br>050 125 W             | 92-6337-8809 |
| SN63PB37 | 245 | 0.6mm  | 58 | No |    | 245 58 Sn63Pb37<br>0.6mm 1/2kg Spl        | 40500992     |
| SN63PB37 | 245 | 0.6mm  | 58 | No |    | 245 58 Sn63Pb37<br>0.6mm 1/2kg Spl<br>(D) | 40510019     |
| SN63PB37 | 245 | 0.6mm  | 58 | No | No | 245 6337 58 060M<br>050 125               | 92-6337-8860 |
| SN63PB37 | 245 | 0.8mm  | 50 | No |    | 245 50 Sn63Pb37<br>0.8mm 1/2kg Spl<br>(D) | 40510008     |
| SN63PB37 | 245 | 0.8mm  | 50 | No | No | 245 6337 50 080M<br>050 125               | 92-6337-8800 |

|             |     |       |    |     |    |                                           |              |
|-------------|-----|-------|----|-----|----|-------------------------------------------|--------------|
| SN63PB37    | 245 | 0.8mm | 58 | No  |    | 245 58 Sn63Pb37<br>0.8mm 1/2kg Spl<br>(D) | 40510020     |
| SN63PB37    | 245 | 0.8mm | 58 | No  |    | 245 58 Sn63Pb37<br>0.8mm 1kg Spl          | 40510954     |
| SN63PB37    | 245 | 0.8mm | 58 | No  | No | 245 6337 58 080M<br>050 125               | 92-6337-8801 |
| SN63PB37    | 245 | 0.8mm | 66 | No  |    | 245 66 Sn63Pb37<br>0.8mm 1/2kg Spl<br>(D) | 40510993     |
| SN63PB37    | 245 | 1.0mm | 50 | No  |    | 245 50 Sn63Pb37<br>1.0mm 1/2kg Spl<br>(D) | 40510009     |
| Sn63Pb37    | 245 | 1.0mm | 50 | No  | No | 245 6337 50 100M<br>050 125               | WM0584       |
| SN63PB37    | 245 | 1.0mm | 58 | No  |    | 245 58 Sn63Pb37<br>1.0mm 1/2kg Spl<br>(D) | 40510021     |
| SN63PB37    | 245 | 1.0mm | 58 | No  | No | 245 6337 58 100M<br>050 125               | 92-6337-8846 |
| SN63PB37    | 245 | 1.0mm | 66 | No  | No | 245 6337 66 100M<br>050 125               | 92-6337-8825 |
| SN63PB37    | 245 | 1.2mm | 50 | No  |    | 245 50 Sn63Pb37<br>1.2mm 1/2kg Spl<br>(D) | 40510011     |
| SN63PB37    | 245 | 1.3mm | 66 | No  |    | 245 66 Sn63Pb37<br>1.3mm 1/2kg Spl        | 40500035     |
| SN63PB37    | 245 | 1.5mm | 50 | No  |    | 245 50 Sn63Pb37<br>1.5mm 1/2kg Spl<br>(D) | 40510012     |
| SN63PB37    | 245 | 1.5mm | 58 | No  |    | 245 58 Sn63Pb37<br>1.5mm 1/2kg Spl<br>(D) | 40510024     |
| SN63PB37    | 245 | 1.5mm | 66 | No  |    | 245 66 Sn63Pb37<br>1.5mm 1/2kg Spl<br>(D) | 40511011     |
| Sn63Pb37    | 245 | 1.6mm | 50 | No  | No | 245 6337 50 160M<br>050 125               | WM0591       |
| Sn95Ag5     | 245 | 1.0mm | 58 | Yes | No | 245 95A5 58 100M<br>050 125 W             | WM2655       |
| SN96.5AG3.5 | 245 | 0.015 | 58 | Yes |    | SN96.5AG03.5<br>#58/245 .015 1 LB<br>SPL  | 2470408843   |
| SN96.5AG3.5 | 245 | 0.02  | 58 | Yes |    | SN96.5AG03.5<br>#58/245 .020 1 LB<br>SPL  | 2470408834   |
| SN96.5AG3.5 | 245 | 0.031 | 50 | Yes |    | SN96.5AG03.5<br>#50/245 .031 1 LB<br>SPL  | 2470408800   |
| SN96.5AG3.5 | 245 | 0.031 | 58 | Yes |    | SN96.5AG03.5<br>#58/245 .031 1 LB<br>SPL  | 2470408801   |
| SN96.5AG3.5 | 245 | 0.031 | 66 | Yes |    | SN96.5AG03.5<br>#66/245 .031 1 LB<br>SPL  | 2470408802   |
| SN96.5AG3.5 | 245 | 0.04  | 58 | Yes |    | SN96.5AG03.5<br>#58/245 .040 1 LB<br>SPL  | 2470408846   |
| SN96.5AG3.5 | 245 | 0.062 | 58 | Yes |    | SN96.5AG03.5<br>#58/245 .062 1 LB<br>SPL  | 2470408803   |
| SN96.5AG3.5 | 245 | 0.5mm | 58 | Yes |    | 245 58 Sn96.5Ag3.5<br>0.5mm 1/2kg Spl     | 40500689     |
| SN96.5AG3.5 | 245 | 0.8mm | 58 | Yes |    | 245 58 Sn96.5Ag3.5<br>0.8mm 1lb spool     | 40500736     |

## PROCESS COMPATIBLE PRODUCTS

951 SOLDERING FLUX

952-D6 SOLDERING  
FLUX



> [VIEW PRODUCT](#)  
> [DATA SHEET](#)  
> [SDS\\_ENGLISH](#)



> [VIEW PRODUCT](#)  
> [DATA SHEET](#)  
> [SDS\\_ENGLISH](#)



> [FIND DISTRIBUTOR](#)

Search Kester.com

OUR COMPANY  
[OVERVIEW](#)  
[CORPORATE CITIZENSHIP](#)  
[EMPLOYMENT](#)

PRODUCTS  
[SOLDER PASTE](#)  
[LIQUID SOLDER FLUX](#)  
[TACKY SOLDER FLUX](#)  
[PREFORMS](#)  
[BAR SOLDER](#)  
[SOLDER WIRE](#)  
[OTHER](#)

DOWNLOADS  
[SDS](#)  
[ENVIRONMENTAL](#)  
[DATA SHEETS](#)  
[CATALOGS](#)

KNOWLEDGE BASE  
[FAQ](#)  
[ALLOY PROPERTIES](#)  
[LEAD-FREE SOLUTIONS](#)

CONTACT  
[DISTRIBUTION](#)  
[SALES](#)  
[CUSTOMER SERVICE](#)  
[LINKEDIN](#)