



**Part Number :** [197084003](#)  
**Product Description :** PCB Tab Quick Disconnect, Male, for Wire, Metal Strip, Tab 4.75 x 0.51mm  
**Series Number :** 19708  
**Status :** Active  
**Product Category :** Quick Disconnects



## Documents & Resources

**Drawings**  
[197084003\\_sd.pdf](#)  
[PK-19511-601-001.pdf](#)

**3D Models and Design Files**  
[197084003\\_stp.zip](#)

**Specifications**  
[PS-19708-001-001.pdf](#)  
[PS-19902-011-001.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Quick Disconnects
Series	19708
Description	PCB Tab Quick Disconnect, Male, for Wire, Metal Strip, Tab 4.75 x 0.51mm
Product Name	PCB Tab
Type	Quick Disconnect
UPC	800754886840

#### Agency

UL	E79133
----	--------

#### Electrical

Voltage - Maximum	N/A
-------------------	-----

#### Physical

Barrel Type	N/A
Gender	Male
Glow-Wire Capable	No
Insulated	No
Insulation	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.541/g
Orientation	PCB Straight Tab

Packaging Type	Reel
Polarized to Mating Part	No
Tab Thickness	0.51mm
Tab Width	4.75mm
Wire Insulation Diameter	N/A
Wire Size (AWG)	N/A

---

This document was generated on Mar 09, 2025