
molex



Part Number : 395350522
Product Description : 5.08mm Pitch Eurostyle Vertical PCB Header, with Threaded Retention Inserts, Gold (Au) Plated, Black, 22 Circuits
Series Number : 39535
Status : Active
Product Category : Terminal Blocks and Barrier Strip

Documents and Resources

Drawings

395350522_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

PS-39500-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS

Downloaded from Arrow.com.

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	39535
Description	5.08mm Pitch Eurostyle Vertical PCB Header, with Threaded Retention Inserts, Gold (Au) Plated, Black, 22 Circuits
Application	Wire-to-Board
Component Type	PCB Header
Product Name	Eurostyle Pluggable
Type	PCB Terminal Blocks and Connectors
UPC	822350490436

Agency

UL	E48521

Electrical

Current - Maximum per Contact	15.0A
Voltage - Maximum	300V

Physical

Downloaded from Arrow.com.

Circuits (Loaded)	22
Color - Resin	Black
Entry Angle	N/A
Lock to Mating Part	Yes
Number of Rows	1
Orientation	Vertical
Panel Mount	No
PCB Thickness - Recommended	3.20mm
PC Tail Length	5.08mm
Pitch - Mating Interface	5.08mm
Pitch - Termination Interface	5.08mm
Polarized to Mating Part	Yes
Shrouded	Closed Ends
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire Size (AWG)	N/A

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
5.08mm Pitch Eurostyle Horizontal Plugs	39534
5.08mm Pitch Eurostyle Plugs	39537
Mates With	Most 5.08mm Pitch Industry Standard Plugs

Downloaded from Arrow.com.