

Search within category

GO

BUY NOW

DESIGN / INSTALL



CJSH6X88TGY

Category 6A, RJ45, 8-position, 8-wire shielded spring shuttered universal jack module, Black.

Specs

Packaging Details

Documents

★ Add to Favorites

🛒 Add to BOM

Application	Shielded
Color	Black
Depth (In.)	1.50
Depth (mm)	38.1
Height (In.)	0.75
Material	ABS/Tin Plated Over Phosphorous Bronze//Plastic
Module Type	Mini-Com
Operating Temperature	14°F to 149°F (-10°C to 65°C)
Performance Level	Category 6A
Storage Temperature	-40°F to 158°F (-40°C to 70°C)
Termination Style	Giga-TX (TG Style)
Wiring Scheme	T568A/T568B
RoHS Compliancy Status	Compliant
Min. Order Qty.	1