

Safe-IT Multi-Device UV Charging Cart, Hospital-Grade, 32 USB Ports, iPad and Android Tablets, Antimicrobial, White

MODEL NUMBER: **CSC32USBWHG**



Charges, syncs, secures, organizes and sanitizes up to 32 USB devices in healthcare, education, retail, warehouse and office settings.

Features

Mobile Charging Cart Accommodates up to 32 USB Mobile Devices This 120V charging station provides USB charging, secure storage, cord management and surface sanitization for as many as 32 iPad, iPod, iPhone, Android, Surface, Kindle and other USB tablets and smartphones. The USB ports deliver the fastest charging supported by each connected device, up to 2.4A per port. A USB uplink port connects to a host computer for wired syncing. The tablet charging station is recommended for healthcare facilities, classrooms, businesses, government agencies, restaurants, hotels and anywhere else that uses mobile devices on a daily basis.

UV Light Helps Sanitize Devices without Potentially Dangerous Heat, Liquids or Chemicals The CSC32USBWHG helps reduce the presence of germs on Chromebooks, laptops and tablets. Built-in ultraviolet lights help disinfect electronic devices at the touch of a button by destroying most microbes without the use of damaging heat, liquids or chemicals. The germicidal UVC bulbs are on a timer to control the amount of UV exposure the devices receive. An LED on the exterior of the cabinet indicates when the doors are closed and the start button can be pressed to activate the 10-minute timer. A second LED indicates when the UVC lights are on. If a door is opened during sanitization, the lights automatically shut off for safety.

Exclusive Antimicrobial Protection Fights Surface Bacteria The charging cabinet's interior and exterior surfaces are protected by an antimicrobial coating which helps prevent the growth of bacteria, viruses, fungi, mold and mildew. The coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

Locking Steel Enclosure Keeps Valuable Equipment Safe and Secure Constructed from heavy-duty steel, this charging cart provides safe, secure storage. The split front doors lock with the included keys to help prevent theft, damage and tampering. For extra security, the front door can be fastened with a user-supplied padlock. Flow-through ventilation helps protect against overheating, and the specially coated shelves help prevent device scratches and scuffs.

Moving Your Devices from Room to Room Is Easy Four pre-installed swivel casters with large non-marking wheels improve the ride over uneven surfaces, including carpeting and thresholds, and lock to help prevent unwanted movement. The reversible wide-grip handle makes the cart easy to control.

Highlights

- 32 internal USB-A ports charge mobile devices with optimum charge level up to 2.4A
- Ultraviolet (UVC) lights help disinfect devices without use of damaging heat or chemicals
- Antimicrobial protection aids in resisting the growth of bacteria, viruses, fungi, mold and mildew
- Steel enclosure locks with included keys to discourage theft, damage and tampering
- 10-ft. (3.05 m) cord with NEMA 5-15P HG plug allows great flexibility in reaching AC outlets

Applications

- Charge up to 32 Apple, Android, Microsoft, Amazon and other USB tablets and smartphones in medical facilities, schools, businesses and government organizations that rely on the daily use of mobile devices
- Easily and safely transport connected devices from room to room with a smooth, controlled ride
- Sanitize your devices with ultraviolet light to reduce the presence of germs

Package Includes

- CSC32USBWHG Hospital-Grade 32-Device UV Charging Cart, White
- Cart handle
- Input cord wrap
- (12) Hex screws
- Hex key
- (2) Keys
- Owner's manual

Well-Organized to Avoid Confusing Cable Clutter Cables and connectors run through strain relief bushings, keeping them organized and out of the way, and are protected by blanking panels. Adjustable dividers accommodate up to 16 devices per shelf. Front doors open at least 180 degrees to allow maximum access to the interior. A power cord wrap keeps the input cord out of the way when moving the charging station. Access grommets allow the 10-ft. (3.05 m) cord with hospital-grade NEMA 5-15P plug to extend through either side of the cart, allowing great flexibility in reaching AC outlets.

Specifications

OVERVIEW	
UPC Code	037332240156
Product Type	Multi-Device Charger
Charging Form Factor	Mobile Cart
Functions	Charge; Secure; Sync; Sanitize
Device Compatibility	Tablet; Phone
Device Slots	32
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Input Frequency	50 / 60 Hz (auto-select)
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
POWER	
Power Consumption (Watts)	112
CHARGING	
Number of Charging Ports	32
Total Charging Amps	80A
Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports Details	Pass through
Charging Ports / Amps	(32) 2.4A
Overcharge Protection	No
Charging Amps per Port	2.4A
PHYSICAL	
Color	White

Material of Construction	Steel
Shipping Dimensions (hwd / in.)	39.96 x 23.62 x 33.66
Shipping Weight (kg)	70.50
Slot Dimensions - Bottom (hwd / in.)	10.5 x 1.5 x 15.4
Slot Dimensions - Bottom (hwd / mm)	267.3 x 38.2 x 390.5
Slot Dimensions - Top (hwd / in.)	10.5 x 1.5 x 15.4
Slot Dimensions - Top (hwd / mm)	267.3 x 38.2 x 390.5
Unit Dimensions (hwd / in.)	36.100 x 34.800 x 20.200
Unit Dimensions (hwd / cm)	91.69 x 88.39 x 54.86 (with handle installed)
Unit Weight (lbs.)	130.67
Unit Weight (kg)	59.27
Number of Shelves	2
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	Yes
Built-In Circuit Breaker	Yes
Cord Management	Yes
Overcurrent Protection	Yes
EMI/RFI Line Noise Protection	Yes
Flow-Through Ventilation	Yes
Antibacterial	No
IP68 Rated	No
IP20 Rated	No
UV Sterilization	Yes
Locking	Yes
Lock Type	Key; Padlock (User Supplied)
STANDARDS & COMPLIANCE	
Product Certifications	NOM (Mexico); UL 60950-1
Product Compliance	RoHS; CE (Europe); EIA/ECA-310-E; REACH; FCC Part 15 Class B (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty
CATEGORY PAGE FILTERS (Y/N ONLY)	

External Receptacle	No
---------------------	----