Specifications



Photo is representative





Eaton FP0906R1-R28-R

Eaton FP0906 inductor, 0.28 uH, 51 A Irms, 34 A ISAT, 0.304 mΩ resistance, SMT mounting, Ferrite, 2-pins, 600 qty.

General specifications	
PRODUCT NAME	Eaton FP0906 inductor
CATALOG NUMBER	FP0906R1-R28-R
UPC	051712301657
PRODUCT LENGTH/DEPTH	9.6 mm
PRODUCT HEIGHT	8 mm
PRODUCT WIDTH	6.4 mm
PRODUCT WEIGHT	2.07 g
COMPLIANCES	RoHS Compliant
PRODUCT TYPE	Inductor

Powering Business Worldwide

Downloaded from Arrow.com.

Product specifications

TYPE	Inductor
MOUNTING	SMT
IRMS	51 A
ISAT	34 A
PACKAGE QUANTITY	600
MATERIAL	Ferrite
FREQUENCY RATING	Up to 2 MHz
CONTACT CONFIGURATION	Two-pin
TEMPERATURE RATING	-40 to 125 °C
RESISTANCE	0.304 mΩ
SERIES	FP0906

Resources

SPECIFICATIONS AND DATASHEETS	Eaton FP0906 high current power inductors data sheet Eaton Specification Sheet - FP0906R1-R28-R

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Downloaded from Arrow.com.