

Rev	AWO #	Description	Date	Appr
-		RELEASED	2/22/21	


APPROVED: _____


DATE: _____ TITLE: _____





RECOMMENDED PCB LAYOUT





SPECIFICATIONS:

Material:
Insulator: PA, rated UL 94V-0
Insulator color: Green
Pin Header: Copper Alloy, Tin plated

Electrical:
Voltage rating: 600 V
Current rating: 51 A
Dielectric withstanding voltage: 2,200 V for 1 minute

Mechanical:
Wire range: 18~4AWG
Wire strip length: 17-18mm

Temperature Rating:
Operating temperature: -40°C to +105°C

Environmental:
Lead free, RoHS compliant.

RoHS COMPLIANT

Positions: 02 thru 18
A= .591 [15.00] x No. of Space + .449 [11.40]
B= .591 [15.00] x No. of Space

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
DRAWN	LH	2/22/21
CHECKED	NL	2/22/21
APPROVED		

ADAM TECH
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE: .591[15.00] PITCH SPRING CLAMP TERMINAL BLOCKS, RIGHT ANGLE

SIZE	PART NO.	REV.
X	EB171A-XX-K	-

REF: S00067C | SCALE: NTS | SHEET 1 OF 1

Downloaded from Arrow.com.