

Honeywell Sensing and Control

Search



narrow your search

Products

- Controls Monitoring and Lighting (286)
- Machine Safety (1727)
- Sensors (6165)
- Switches (9781)
- Wireless (45)

Technology

- Control and Instrumentation (890)
- Electromechanical (9307)
- Magnetic (541)
- Platinum thin film (56)
- Thick Film (1372)
- More...

new products

New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site
WGLA and WPMM
XYR6000™

[find out more](#)

white papers

- Wireless Switches Offer Unlimited Benefit
- Basic Switches Are Not Created Equal
- Applying Precision Switches
- Sensors for Medical Devices
- New Ways to Measure Torque
- Choosing Safety Switches
- Specifying Hour Meters

Need help?

[Click here to contact us](#)

GSXA42D

(Home : Products : Machine Safety » MICRO SWITCH™ Safety Switches » Electromechanical » GSX)



Actual product appearance may vary.

GSX Series, Explosion-Proof Safety Switch, 0.5 in NPT housing, 2NC/1NO top roller lever

[Sales & Service](#)[Distributor Inventory](#)[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

Product Specifications

Product Type	Safety Limit Switch
Actuator	Top Roller Lever
Switch Type	2NC/1NO Positive Break, Slow Acting, BBM
Contact Material	Silver
Termination Type	0.5 in NPT Housing
Ampere Rating	10 A (Thermal)
Housing Material	Zinc die-cast
Housing Type	0.5 in NPT Housing
Series Name	GSX
Sealing	IP67; NEMA 1, 3, 4, 12, 13
Agency Approvals and Standards	cULus, ATEX, IEC Ex
Expected Mechanical Life	1 Million
Operating Temperature	-40 °C to 70 °C [-40 °F to 158 °F]
Availability	Global
UNSPSC Code	302119
UNSPSC Commodity	302119 Switches and Controls and Relays
Comment	Div. 1, Class I, Groups B, C, & D; Div. 1, Class II, Groups, E, F, & G; II 2 G, Ex d IIC T6; II 2 D, Ex d IIC A21 T85C

contacts

Customer Service
Technical Support
Global Sales & Service
View Site Demo
Site Comments?

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



Meet Dr. Larry

my links

Login to iCOM
Login to Rep/AD Portal
Login to Digital University

News Center

Honeywell Introduces TruStability® NSC Series, Uncompensated / Unamplified Board Mount Pressure Sensors

HONEYWELL EXPANDS ITS LIMITLESS™ PLATFORM WITH THE LAUNCH OF ITS GLOBALLY AVAILABLE INDUSTRIAL WIRELESS RECEIVER

HONEYWELL EXTENDS ITS TRUSTABILITY® PRESSURE SENSOR PRODUCT LINE WITH A SINGLE SIDE LIQUID MEDIA OPTION

HONEYWELL ADDS NEW 100° AND 180° ARC CONFIGURATIONS TO ITS SMART POSITION SENSOR PORTFOLIO

HONEYWELL INTRODUCES ITS HAWK™ RESOLVERS 1-INCH SERIES, FULLY HOUSED CONFIGURATION

HONEYWELL INTRODUCES MICROPOWER OMNIPOLAR DIGITAL HALL-EFFECT SENSOR ICS WITH LOW SUPPLY VOLTAGE AND ULTRA LOW TYPICAL CURRENT

**MICRO SWITCH
Anniversary site**