

## Han CGM-P M40x1,5 D.22-32mm black



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 19 00 000 5189  |
| Specification      | Han CGM-P M40x1,5 D.22-32mm black   |
| HARTING eCatalogue | <a href="https://harting.com/19000005189">https://harting.com/19000005189</a> |

### Identification

|                          |             |
|--------------------------|-------------|
| Category                 | Accessories |
| Series of hoods/housings | Han® CGM-P  |
| Type of accessory        | Cable gland |

### Technical characteristics

|  |  |
|--|--|
| Tightening torque                      | ≤10 Nm (depending on the cable and the seal insert used) |
| Wrench size                            | 53   |
| Limiting temperature                   | -40 ... +100 °C  |
| Degree of protection acc. to IEC 60529 | IP68<br>IP69 / IPX9K acc. to ISO 20653                   |
| Size                                   | M40  |
| Clamping range                         | 22 ... 32 mm   |
| Width across corners                   | 58.8 mm  |

### Material properties

|   |                      |
|---|----------------------|
| Material (cable glands)                   | Polyamide (PA)       |
| Colour (cable gland)                      | RAL 9005 (jet black) |
| Material (seal)                           | NBR                  |
| Material flammability class acc. to UL 94 | V-0                  |
| RoHS                                      | compliant            |
| ELV status                                | compliant            |
| China RoHS                                | e                    |
| REACH Annex XVII substances               | Not contained        |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |               |
|--------------------------------------|---------------|
| REACH ANNEX XIV substances           | Not contained |
| REACH SVHC substances                | Not contained |
| California Proposition 65 substances | Not contained |

## Specifications and approvals

|           |  |
|-----------|--|
| UL / CSA  | UL 514B QCRV.E479780<br>CSA-C22.2 No. 18.3 QCRV7.E479780 |
| Approvals | DNV GL   |

## Commercial data

|                                |   |
|--------------------------------|---|
| Packaging size                 | 1   |
| Net weight                     | 55 g                                      |
| Country of origin              | Germany                                   |
| European customs tariff number | 39174000                                  |
| GTIN                           | 5713140192942                             |
| eCl@ss                         | 27140801 Screwed cable gland (electrical) |
| ETIM                           | EC000441                                  |
| UNSPSC 24.0                    | 39121431                                  |