



Pushing Performance  
Since 1945

# Han GND module, female



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 001 3132
Specification	Han GND module, female
HARTING eCatalogue	<a href="https://harting.com/09140013132">https://harting.com/09140013132</a>

## Identification

Category	Inserts
Series	Han® GND

## Version

Termination method	Crimp termination Axial screw termination
Gender	Female
Number of contacts	1
Details	Please order contacts separately.

## Technical characteristics

Conductor cross-section	10 ... 35 mm²
Wire outer diameter	≤13 mm
Insulation resistance	>10 <sup>10</sup> Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

## Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	Yellow
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant



**Pushing Performance**  
Since 1945

## Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

## Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984
UL / CSA	UL 1977 ECBT2.E235076

## Commercial data

Packaging size	2
Net weight	8.32 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140019393
eCl@ss	27440205 Contact insert for industrial connectors
ETIM	EC000438
UNSPSC 24.0	39121522