

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0391001904

Status:

Active

Overview:

Eurostyle™ Two-Screw Barrier Strips

Description:

8.00mm Pitch Beau™ Eurostyle™ Two-Screw Terminal Strips, 4 Circuits, Low Profile

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Terminal Blocks

Series

39100

Application

Wire-to-Wire

Component Type

One Piece

Overview

Eurostyle™ Two-Screw Barrier Strips

Product Name

Eurostyle™ Two Screw

Type

Barrier Strip

UPC

78172545142

Physical

Circuits (Loaded)

4

Circuits (maximum)

4

Color - Resin

White

Entry Angle

Horizontal

Lock to Mating Part

None

Material - Metal

Stainless Steel

Material - Resin

Nylon

Net Weight

4.535/g

Number of Rows

2

Orientation

Vertical

PCB Retention

Yes

Panel Mount

Mounting Holes Between Circuit

Pitch - Mating Interface

8.00mm

Pitch - Termination Interface

8.00mm

Polarized to Mating Part

No

Stackable

No

Temperature Range - Operating

-40°C to +105°C

Wire Size AWG

12, 14, 16, 18, 20, 22

Electrical

Current - Maximum per Contact

20.0A

Voltage - Maximum

300V

Material Info

Engineering Number

M800-01-04-5

Reference - Drawing Numbers

Sales Drawing

SD-39100-012



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per -ED/01/2017 (12 January 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

39100 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION