


D1RFRD006


REVISION RECORD				
REV	ECO	DESCRIPTION	DRFT	DATE
2		Drawing emend	WF	12/13/05"
3		增加VDE、CE认证标志	LJH	01/14/08"






SECTION A-A





VIEW-B



Notes:

1. Pitch: 5.08mm Poles:2-24p
2. Rated voltage/current:UL 300V/15A
   VDE 320V/20A
3. Insulation resistance: 5000MΩ/1000V
4. Withstanding voltage: AC1500V/1Min
5. Wire range: 28-12AWG 2.5mm²
6. Temp.Range: -40° C~+105° C
7. Torque: 4.08kgf.cm(3.5Lb.in)
8. Undimensioned Tolerances:

Pitch range in mm			Naminal dimension range in mm					—
	over 6 to 10	over 10 to 24		over 30 to 60	over 60 to 100	over 100 to 150	over 150	⌒
to 6			to 30					▱
±0.10	±0.15	±0.25	±0.2	±0.3	±0.5	±0.7	±1.0	0.05/10

ITEM	NAME OF PART	NO. OF PART	Q"TY	MATERIAL	NOTES
1	2EDGK-5.08-Housing	1005A0YXXA(H)	1	PA66	UL94V-0
2	2EDGK-5.08-Cover	1005C0YXXA(H)	1	PA66	UL94V-0
3	2EDG "—"Screws-M2.5	S000001370(H)	XX	Steel	$Cr^{3+}Zn$
4	DG128 Brass cage	X000000020(H)	XX	Brass	Ni plated
5	2EDG Clamp	1005B00010(H)	XX	Phoshor bronze	Ni plated

DETACHED LISTS

MM (INCH)

TOLERANCES EXCEPT AS NOTED

MM
.0 ±
.00 ±
.000 ±

ANGLES ± 1°

THIRD ANGLE PROJECTION

DFTD Haoyh	DATE 04/18/'05
CHKD	DATE
MFD	DATE
APPVL	DATE
MATERIAL :	
G.E :	
FINISH:	
SCALE : 1:1	

DEGSON®

宁波高正电子有限公司
DEGSON ELECTRONICS CO., LTD

NAME

2EDGK-5.08-XXP-1Y-00A(H)

DRAWING NO. 2EDGK-5.08-E08 /PART NO.

SIZE A3

REV T3 01/14/08"

DO NOT SCALE DRAWING

SHEET 1 OF 1

Downloaded from Arrow.com.