



Technical Data

03.07.2023

Conductive Tapes – Electrical Semi-Conducting Tape
HelaTape Shield 310

HTAPE-SHIELD310

Article Number 711-00000

Material:	Ethylene Propylene Rubber (EPR)
Colour:	Black (BK)
Operating Temperature :	-40 °C to +90 °C
Thickness (T):	0.76 mm
Width (W):	19 mm
Length (L):	4.6 m
Breaking Strength:	2 N/10 mm
Adhesion to Backing:	2 N/10 mm
Adhesion to Steel:	2.2 N/10 mm
Tensile Strength:	2.0 MPa
Elongation at break:	600 %
Shelf Life:	5 years
Storage Temperature:	+23 °C



We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved