Product Line

- DeepTronica
- Single Pair Ethernet
- ZConnect
- Ceres
- X-Lok
- M Series
  - Accessory
  - M5
  - Guided M8
  - M8
  - M10.5
  - M12 (A)
  - M12 (B)
  - M12 (D)
  - M12 (I)
  - M12 (K)
  - M12 (L)
  - M12 (S)
  - M12 (T)
  - M12 (X)
  - M23
- FLOS & FLOS+
- Power
- RBL
- HS-Lok
- NMEA 2000
- Heavy Duty Shielded
- RJ
- USB
- SSL
- HDMI
- DVI
- Fiber Optic
- RF
- Cable Joiner
- Cable Gland
- Pressure Relief Vent
- LED Light Guide
- D-Sub
- ALTW Emporium





SLD-D004001

- Operating Temperature: -40°C ~ +105°C
- Transmission Speed: N/A
- Shielded: Plastic, Non-shielded
- Jacket Material: N/A
- Certificate: N/A

You must login first for view the price

Quantity − 1 +


Add to Cart | Inquiry

Can't find? Customize your part

Mating Pair & Accessories

Connector Type

Search



M Series, M12, D...	M Series, M12, D...	M Series, M12, D...	M Series, M12, D...	M Series, M12, D...	M Series, M12, D...
M12D-04PFFC-... -20°C ~ +85°C	M12D-04PFFC-... -20°C ~ +85°C	M12D-04PFFC-... -20°C ~ +85°C	M12D-04PFFC-... -20°C ~ +85°C	M12D-04PFFC-... -20°C ~ +85°C	M12D-04PFFC-... -20°C ~ +85°C
− 0 +	− 0 +	− 0 +	− 0 +	− 0 +	− 0 +

Add to Cart | Inquiry

Specifications | Download / CAD

Nominal Current: **4A**	Connector Type: **Insert**
Shielded: **Plastic, Non-shielded**	No. of Contacts: **04**
Connector Gender: **Male**	Backshell: **N/A**
Mating Style: **Screw Thread**	IP Rating: **Non-waterproof**
Assembly Style: **Solder**	

More Options

People Also Bought



SLD-D004001 | AB-BB03FL-BBBR-... | ABD-06BFFM-SL7A05 | AD-02BFFM-QL8P10 | MSAP-08BFFM-...

Downloaded from Arrow.com.