

 Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



Always EU RoHS/ELV Compliant (Statement of Compliance)

? Receptacle
? Tab Fit = 2.79 x 0.51 mm
? Board Mount = No
? Receptacle Style = Straight
? Non-Insulation Support

[View all Features](#) | [Find Similar Products](#)

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

Product Drawings:

[RECEPTACLE, FASTON, 2.79 \[110\] SERIES](#) (PDF, English)

Catalog Pages/Data Sheets:

? None Available

Product Specifications:

? None Available

Application Specifications:

[FASTON Straight Receptacles with "F" -" Crimp Feature" \(PDF, English\)](#)

[Wire Preparation And Crimp Inspection Guide \(PDF, English\)](#)

Instruction Sheets:

? None Available

CAD Files:

? None Available

List all Documents

Additional Information:

? Product Line Information

Related Products:

? Tooling

Product Features

Product Type Features:

? Product Type = Receptacle
 ? Tab Fit (mm [in]) = 2.79 x 0.51 [.110 x .020]
 ? Receptacle Style = Straight
 ? Insulation Support = Non -Insulation Support
 ? Wire/Cable Type = Regular Wire
 ? Insertion Force = Normal
 ? Material = Brass
 ? Finish = Pre -Tin
 ? Crimp Type = "F"
 ? CSA Certified = Yes
 ? Comment = Dimple at special location; Side Feed

Mechanical Attachment:

? Board Mount = No

Body Related Features:

? Weld Tab = Without

? Wire Range (mm [AWG]) = (2) 0.80 - 0.90 ² [(2) 18], 0.80 - 2.00 ² [18-14]

? UL Rating = Listed

? Stock Thickness (mm [in]) = 0.25 [0.010]

Industry Standards:

- ? RoHS/ELV Compliance = RoHS compliant, ELV compliant
- ? Lead Free Solder Processes = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

? Packaging Method = Strip

Other:

? For Hermetic Header Tab = No

? Brand = AMP