








REV.	DATE	DESCRIPTION
NC	03/04/08	INITIAL RELEASE



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:
0.5 - 8mm $\pm$ 0.20mm
8 - 30mm $\pm$ 0.40mm
30 - 120mm $\pm$ 0.50mm

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:
.020 - .315 $\pm$ 0.007"
.315 - 1.180 $\pm$ 0.015"
1.180 - 4.724 $\pm$ 0.020"

DO NOT SCALE DRAWING

APPROVALS	DATE
DRAWN G.R.S.	03/04/08
CHECKED	
ISSUED	
SHEET 1 OF 1	
CAD FILE	
C:/122/122463RP-50.DWG	

Amphenol Connex

PART DESCRIPTION

TNC REVERSE POLARIZED BULKHEAD DIRECT
SOLDER JACK (.085", .086" CABLE 50ohms)

PART NO.

122463RP-50

DWG. NO.

122463RP-50.DWG

REV. NC

SIZE A

SCALE NA

DESCRIPTION

MATERIAL

FINISH

QTY

8				
7				
6	INSULATOR	TEFLON	NATURAL	1
5	HEX NUT	BRASS	NICKEL	1
4	LOCK WASHER	BRASS	NICKEL	1
3	CONTACT PIN	BRASS	GOLD	1
2	INSULATOR	TEFLON	NATURAL	1
1	BODY	BRASS	NICKEL	1